



## Main

Commercial Status	Commercialised
Range	ClimaSys CV
Category	Fan
Type of filter	Standard
Flow rate	Free flow rate with standard filter: 193 m <sup>3</sup> /h at 60 Hz Free flow rate with standard filter: 165 m <sup>3</sup> /h at 50 Hz
[Us] rated supply voltage	175...253 V
Input voltage	230 V 50/60 Hz

## Complementary

Absorbed power	14.3 W 60 Hz 16.3 W 50 Hz
[In] rated current	0.94 A 60 Hz 0.12 A 50 Hz
Noise level	50...51 dB
Bearing type	Ball
Height	External: 268 mm
Width	External: 248 mm
Depth	External: 104 mm
Cut-out dimensions	223 x 223 mm
Product weight	1.14 kg
Material	Injected thermoplastic (ASA PC) for outlet grille
Colour	Outlet grille: grey RAL 7035
Ambient air temperature for operation	-20...60 °C
Ambient air temperature for storage	-40...70 °C
Maximum pressure	50 Pa flow rate 0 m <sup>3</sup> /h
Electrical connection	Faston connector
IP degree of protection	IP54
Device composition	1 power cord 1 cut-out template 1 outlet grille front 1 filter front of axial motor 2 protective grille on the front and rear surfaces 1 axial motor
Condition of use	Outside temperature must be 5 °C lower than inside temperature Filter must be cleaned and replaced regularly Surrounding environment must be relatively clean Overfrequent filter replacement should be avoided Flow rates depends on the work point, see ProClima software

## RoHS compliance

RoHS EUR status	Compliant
RoHS EUR conformity date(YYYY)	0940

## Contractual warranty

Period	18 months
--------	-----------