

**Product Specs**

Blade Length
1.18 in

Blade Material
60CrV

Gauge Cutting Capacity
18ga

Handle Length
4.33 in

Durable titanium nitride-coated chrome molybdenum blades. Long lasting, for up to 50,000 cuts in cold rolled steel.

Features & Benefits

Cuts up to 18ga (1.2mm) cold-rolled steel or 22ga (0.7mm) stainless steel.

Flush hardware helps prevent catching on materials while cutting.

Auto release mechanism provides for fast one handed operation.

Induction hardened cutting edge stay sharp longer (compared to non-induction hardened blades).

1/4" blade markings for quick precise cuts. Laser etched for permanency.

