

9PC. EXTRA LONG BALL POINT WITH HANDLE (METRIC) **New**

PART NO.	CONTENT			G.W.(kg)
09124	9PC.	6	24	16.8

DESCRIPTION:
2mm, 2.5mm, 3mm,
4mm, 5mm, 6mm,
7mm, 8mm, 10mm



8PC. EXTRA LONG TORX® SET **New**

PART NO.	CONTENT			G.W.(kg)
09701	8PC.	12	72	7.1

DESCRIPTION:
TT6, TT7, TT8,
TT9, TT10, TT15,
TT20, TT25



9PC. EXTRA LONG TORX® SET **New**

PART NO.	CONTENT			G.W.(kg)
09702	9PC.	6	48	18.4

DESCRIPTION:
TT10, TT15, TT20,
TT25, TT27, TT30,
TT40, TT45, TT50



8PC. FOLDUP SET (METRIC) **New**

PART NO.	CONTENT			G.W.(kg)
09121	8PC.	12	72	14.3

DESCRIPTION:
1.5mm, 2mm, 2.5mm,
3mm, 4mm, 5mm,
6mm, 8mm



9PC. FOLDUP SET (S.A.E.) **New**

PART NO.	CONTENT			G.W.(kg)
09122	9PC.	12	72	13.3

DESCRIPTION:
1/4", 7/32", 3/16",
5/64", 3/32", 7/64",
1/8", 9/64", 5/32"



8PC. FOLDUP TORX® SET **New**

PART NO.	CONTENT			G.W.(kg)
09123	8PC.	12	72	13.2

DESCRIPTION:
TT9, TT10, TT15, TT20,
TT25, TT27, TT30, TT40



25PC. HEX KEY WRENCH SET (METRIC & S.A.E.) **New**

PART NO.	CONTENT		G.W.(kg)
09120	25PC.	24	19.3

DESCRIPTION:
13 - Long Arm
0.05-1/16", 5/64", 3/32", 7/64", 1/8", 9/64", 5/32", 3/16", 7/32", 1/4", 5/16", 3/8"
12 - Short Arm
0.7mm, 0.9mm, 1.3mm, 1.5mm, 2mm, 2.5mm, 3mm, 4mm, 5mm, 6mm, 8mm, 10mm




EXTRA LONG BALL POINT (METRIC)

PART NO.	SIZE MM	L MM	D MM			G.W. (kg)
80104	1.5	91	1.5	100	1600	2.5
80105	2	103	2	100	640	2.1
80106	2.5	114	2.5	100	480	2.6
80107	3	128	3	100	480	4.0
80108	4	144	4	100	180	3.1
80110	5	163	5	60	120	92.7
80112	6	184	6	50	576	92.7
80114	8	207	8	20	90	8.9
80116	10	233	10	10	120	92.7



DIN 911




EXTRA LONG (METRIC)

PART NO.	SIZE MM	L MM	D MM			G.W. (kg)
80304	1.5	91	1.5	100	600	16.4
80305	2	103	2	100	600	15.8
80306	2.5	114	2.5	100	150	20.1
80307	3	128	3	100	600	31.3
80308	4	144	4	100	300	45.6
80310	5	163	5	60	240	64.6
80312	6	184	6	50	150	59.8
80314	8	207	8	20	120	92.7
80316	10	233	10	10	120	92.7



DIN 911



BALL POINT (METRIC)

PART NO.	SIZE MM	L MM	D MM			G.W. (kg)
81104	1.5	75	1.5	100	1600	6.4
81105	2	82	2	100	600	9.1
81106	2.5	89	2.5	100	600	12.4
81107	3	98	3	100	600	16.4
81108	4	110	4	100	600	15.8
81110	5	125	5	50	750	20.1
81111	5.5	134	5.5	40	600	31.3
81112	6	142	6	40	300	45.6
81113	7	151	7	30	240	64.6
81114	8	161	8	20	150	59.8
81116	10	182	10	10	120	92.7

