

Single phase, non-stabilised dc power supply **GLC 230/24-7,5**



Advantages

- Fuse protection in the input and a fuse protection for the output
- Separate windings
- Capacitor accessories
- Double screw terminals on the output
- DC OK signalling via LEDs
- Panel installation on mounting rails

Applications

Robust direct current power is concentrated on the core task of voltage and power supply.

Standards



Non-stabilised dc power supply / Safety isolating transformer
to VDE 0570 part 2-6, EN 61558-2-6, IEC 61558-2-6, UL 1012

Approvals




UL 5085-1/-2, CSA 22.2 No.66



Single phase, non-stabilised dc power supply GLC 230/24-7,5

Electrical data	
Type	
GLC 230/24-7,5	
Input	
Input rated voltage	230 Vac
Rated frequency	50 - 60 Hz
Output	
Output rated voltage	24 Vdc
Power	180.00 W
Output rated current	7.50 A
Ripple factor	#5 %
Standards	
Classification	Single phase non-stabilised dc power supply / safety isolating transformer
Approvals	
Approvals	cURus (transformer only)
Environment	
Cooling method	by self cooling
Ambient temperature max.	60° C
Safety and protection	
Type	enclosed
Class of Insulation System	E
Protection index	IP 00
Safety class (prepared)	II
Short circuit strength	short-circuit proof
Order numbers	
Order Number	GLC 230/24-7,5

Mechanical data	
Type	
GLC 230/24-7,5	
Terminal and mounting	
Terminals	Screw-type terminals
Fixing method	DIN Rail system TH 35, additional with screws
Measures and weights	
Weight	6.50 kg



Subjects to change.