

77 52 115 ESD

Electronics Diagonal Cutter ESD



- For fine cutting work, e.g. in electronics and fine mechanics
- Electrically discharging handles - dissipative
- Sturdy, zero-backlash box joint
- Low-friction double spring for gentle and even opening
- The mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Cutting edges additionally induction hardened
- With two-colour dual component grips, black/grey
- High-grade special tool steel, forged, multi stage oil-hardened
- Pointed, flat head, with small bevel
- Cutting edge hardness approx. 60 HRC



ESD pliers (electrostatic discharge)




electrostatic energy is discharged through the handles in a gradual and controlled manner

which protects components endangered by electrostatic discharge

in accordance with applicable standards, e.g. IEC TR 61 340-5, DIN EN 61 340-5, SP Method 2472

| | |
|--|----------------------------|
| Article No. | 77 52 115 ESD |
| EAN | 4003773024330 |
| Head | mirror polished |
| Handles | with multi-component grips |
| Style | 5 |
| Cutting capacities medium hard wire (diameter) Ø mm | 0,8 |
| Cutting capacities hard wire (diameter) Ø mm | 0,5 |
| Cutting capacities soft wire (diameter) Ø mm | 0,3 - 1,0 |
| B mm | 14 |
| D mm | 7 |
| A mm | 11 |
| Length mm | 115 |
| Net weight g | 79 |



technical change and errors excepted

