

Snap-in markers - UC-EMP (17X15) SR - 0825423

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Snap-in markers, Sheet, silver, unlabeled, can be labeled with: BLUEMARK CLED, BLUEMARK LED, Plotter, Mounting type: snapped into marker carrier, Lettering field: 17 x 15 mm




Why buy this product

- The UC-EMP ... UniCard labeling range includes markers that can be fitted into existing CARRIER-EMP ... label frames
- Labeling service: Phoenix Contact can custom-label all UniCard markers according to your requirements
- The markers, which are supplied in uniform sheets, can be labeled quickly and easily using the BLUEMARK LED
- The wide temperature range means that the labels can be used in control cabinets as well as the field
- The format automatically ensures printing with a high degree of positioning accuracy
- The sheets provide space for including function texts



Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 365802
Weight per Piece (excluding packing)	6.2 g
Custom tariff number	39269097
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length (b)	17 mm
Width (a)	15 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

General

Color	silver
Components	free from silicone and halogen

Snap-in markers - UC-EMP (17X15) SR - 0825423

Technical data

General

Inflammability class according to UL 94	V2
Material	PA
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	8
Number of individual labels per row	2
Marking mounting type	snapped into marker carrier

Classifications

eCl@ss

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Accessories

Accessories

Magazine

Magazine - P1 UC-MAG 6 - 5146121



Magazine, for CMS-P1-PLOTTER, for accommodating UC-EMP..., UC-EMLP...

Snap-in markers - UC-EMP (17X15) SR - 0825423

Accessories

Marker carriers

Marker carriers - CARRIER-EMP (17X15) - 0827450



Marker carriers, black, unlabeled, Mounting type: Screws, rivets, Lettering field: 17 x 15 mm

Marker carriers - CARRIER-EMP (1000X15) GY - 0829366



Profile, for screwing or riveting, 1000 mm long, for accommodating UC und US materials, height: 15 mm

Marker carriers - CARRIER-EMP (1000X15) TR - 0829530



Marker carriers, transparent, unlabeled, Mounting type: Screws, rivets, Lettering field: 1000 x 15 mm

Marker carriers - CARRIER/L-EMP (1000X15) GY - 0829559



Profile, self-adhesive, 1000 mm long, for accommodating UC and US materials, height: 15 mm

Marker carriers - CARRIER/L-EMP (1000X15) TR - 0829560



Marker carriers, transparent, unlabeled, Mounting type: Adhesive, Lettering field: 1000 x 15 mm
