



739-8418 Data Sheet

ENGLISH

RS Stock number : 739-8418
Type of tool : Air Nibbler
Power source : Compressed air
Maximum permissible operating pressure : 90 psi (6.2 bar)
Recommended operating pressure : 90 psi (6.2 bar)

Features

Push cutting operation
Ideal for tight spaces and intricate shapes
Quick change punch and die
Powerful motor

Specifications

Material: Aluminium
Cutting Capacity: 18 gauge (1.2mm) steel
Free Speed: 2,500RPM
Weight: 0.8kgs / 1.8lbs
Length: 6.14" / 156mm
Min Hose Size: 3/8" / 10mm
Air inlet thread: 1/4"
Sound: 91.2dBA
Vibration: 4.1 m/s²
Ave Air Consumption: 9.9cfm / 280 l/min
Recommended lubrications: 10 Weight SAE Oil

739-8418

Air Nibbler

Technical Data



Declaration of Conformity

We	RS Components Ltd,
declare under our sole responsibility that the	739-8418 – Air Nibbler
conforms with the directive and the standards	2006/42/EEC EN 792-6 ISO 28927