

Burrs



Hartmetallfrässtifte / Fraises limes / Fresas rotativas de metal duro

Cylinder with end cut

Zylinderform - Mit Stirnverzahnung

Cylindre - coupe en bout

Cilindro - con dentado frontal



	d1 mm	1.5	2.4	2.4	3	3	4	4	4	6	6	6	8	
	l1 mm	6	13	13	13	13	13	16	13	19	19	25	19	
	d2 mm	3	2.4	2.4	3	3	4	4	6	3	6	6	6	
	l2 mm	38	38	63	38	63	50	63	50	45	50	75	50	65
	s	GT1052	GT1102	-	GT1202	-	GT1302	-	GT1302-6	GT1242	GT1402	GT1402L	-	GT1502
	d	GT1052D	GT1102D	GT1102DL	GT1202D	GT1202DL	GT1302D	GT1302DL	GT1302D-6	GT1242D	GT1402D	GT1402DL	GT1402D-1	GT1502D
	d-max™	-	-	-	-	-	-	-	-	-	-	-	-	-
	c	-	-	-	-	-	-	-	-	-	-	-	-	-
	k	-	-	-	GT1202K	-	-	-	-	-	GT1402K	-	-	GT1502K
	alu	-	-	-	-	-	-	-	-	-	GTTA140	-	-	-
	I.S.O. Ref.	-	-	-	B031303	B031303	B041304	B041304	B041606	B061303	B061906	B061906	B062506	B081906
	SCTI Nr.	SB-41M	SB-63M	-	SB-43M	-	-	-	SB-13M	SB-51M	SB-1M	SB-1ML3	SB-1ML	SB-2M
	IPC Code	49	49	49	49	49	49	49	25	49	25	25	25	25

	d1 mm	10	10	11	12	12	12	16	16
	l1 mm	19	25	25	19	25	25	25	25
	d2 mm	6	6	6	6	6	8	6	8
	l2 mm	65	70	70	65	70	70	70	70
	s	GT1602	-	-	GT1702	GT1702-1	GT1702-1-8	GT1802-6	GT1802
	d	GT1602D	GT1602D-1	GT1652D	GT1702D	GT1702D-1	GT1702D-1-8	GT1802D-6	GT1802D
	d-max™	GTDX162	-	-	-	GTDX172-1	-	-	-
	c	-	-	-	-	-	-	-	-
	k	GT1602K	-	-	GT1702K	GT1702K-1	-	-	-
	alu	GTTA160	-	-	-	GTTA170	-	-	GTTA180
	I.S.O. Ref.	B101906	B102506	B112506	B121906	B122506	B122508	B162506	B162508
	SCTI Nr.	SB-3M	SB-3ML	SB-4M	-	SB-5M	SB-5M8	SB-6M	SB-6M8
	IPC Code	25	25	25	25	25	25	25	25

Burrs



Hartmetallfrässtifte / Fraises limes / Fresas rotativas de metal duro

RAPIDE® Coated burrs - Cylinder with end cut

RAPIDE® Zylinderform - Mit Stirnverzahnung

RAPIDE® Cylindre - coupe en bout

RAPIDE® Cilindro - con dentado frontal



	d1 mm	1.5	2.4	2.4	3	3	4	4	4	6	6	6	8	
	l1 mm	6	13	13	13	13	13	16	13	19	19	25	19	
	d2 mm	3	2.4	2.4	3	3	4	4	6	3	6	6	6	
	l2 mm	38	38	63	38	63	50	63	50	45	50	75	50	65
	s- RAPIDE®-D	GCZ1052	GCZ1102	-	GCZ1202	-	GCZ1302	-	GCZ1302-6	GCZ1242	GCZ1402	GCZ1402L	-	GCZ1502
	d- RAPIDE®-D	GCZ1052D	GCZ1102D	GCZ1102DL	GCZ1202D	GCZ1202DL	GCZ1302D	GCZ1302DL	GCZ1302D-6	GCZ1242D	GCZ1402D	GCZ1402DL	GCZ1402D-1	GCZ1502D
	d-max™ RAPIDE®-D	-	-	-	-	-	-	-	-	-	-	-	-	-
	c- RAPIDE®-D	-	-	-	-	-	-	-	-	-	-	-	-	-
	k- RAPIDE®-D	-	-	-	GCZ1202K	-	-	-	-	-	GCZ1402K	-	-	GCZ1502K
	alu- RAPIDE®-A	-	-	-	-	-	-	-	-	-	GCZTA140	-	-	-
	I.S.O. Ref.	-	-	-	B031303	B031303	B041304	B041304	B041606	B061303	B061906	B061906	B062506	B081906
	SCTI Nr.	SB-41M	SB-63M	-	SB-43M	-	-	-	SB-13M	SB-51M	SB-1M	SB-1ML3	SB-1ML	SB-2M
	IPC Code	22	22	22	22	22	22	22	22	22	22	22	22	22

	d1 mm	10	10	11	12	12	12	16	16
	l1 mm	19	25	25	19	25	25	25	25
	d2 mm	6	6	6	6	6	8	6	8
	l2 mm	65	70	70	65	70	70	70	70
	s- RAPIDE®-D	GCZ1602	-	-	GCZ1702	GCZ1702-1	GCZ1702-1-8	GCZ1802-6	GCZ1802
	d- RAPIDE®-D	GCZ1602D	GCZ1602D-1	GCZ1652D	GCZ1702D	GCZ1702D-1	GCZ1702D-1-8	GCZ1802D-6	GCZ1802D
	d-max™ RAPIDE®-D	GCZDX162	-	-	-	GCZDX172-1	-	-	-
	c- RAPIDE®-D	-	-	-	-	-	-	-	-
	k- RAPIDE®-D	GCZ1602K	-	-	GCZ1702K	GCZ1702K-1	-	-	-
	alu- RAPIDE®-A	GCZTA160	-	-	-	GCZTA170	-	-	GCZTA180
	I.S.O. Ref.	B101906	B102506	B112506	B121906	B122506	B122508	B162506	B162508
	SCTI Nr.	SB-3M	SB-3ML	SB-4M	-	SB-5M	SB-5M8	SB-6M	SB-6M8
	IPC Code	22	22	22	22	22	22	22	22

Additional lead times may apply on coated burrs.
Längere Lieferzeiten dürfen mit beschichteten Hartmetallfrässtiften gelten.

Délais de livraison peuvent être plus longs pour les fraises limes revêtues.
Las fresas recubiertas pueden tener un plazo de entrega más largo.