

C810 T Slot Cutter Specification

Part NO.	Description	Material	Finish	Cut Length	Overall Length	No. of Flutes	Manf. Dia.	Shank Dia.
C810*6.0	T-Slot Cutters	HSS	BRIGHT	6.0	57,0	6	6	10,0
C810*1/4	T-Slot Cutters	HSS	BRIGHT	1/4	60,5	6	6.35	1/2
C810*5/16	T-Slot Cutters	HSS	BRIGHT	5/16	65,0	6	7.94	1/2
C810*8.0	T-Slot Cutters	HSS	BRIGHT	8.0	61,0	6	8	10,0
C810*3/8	T-Slot Cutters	HSS	BRIGHT	3/8	68,5	6	9.52	1/2
C810*10.0	T-Slot Cutters	HSS	BRIGHT	10.0	65,0	6	10	12,0
C810*7/16	T-Slot Cutters	HSS	BRIGHT	7/16	73,0	6	11.11	1/2
C810*12.0	T-Slot Cutters	HSS	BRIGHT	12.0	69,0	6	12	12,0
C810*1/2	T-Slot Cutters	HSS	BRIGHT	1/2	76,0	6	12.7	1/2
C810*14.0	T-Slot Cutters	HSS	BRIGHT	14.0	79,0	6	14	16,0
C810*5/8	T-Slot Cutters	HSS	BRIGHT	5/8	101,5	8	15.88	1.
C810*16.0	T-Slot Cutters	HSS	BRIGHT	16.0	76,0	6	16	16,0
C810*18.0	T-Slot Cutters	HSS	BRIGHT	18.0	98,0	8	18	25,0
C810*3/4	T-Slot Cutters	HSS	BRIGHT	3/4	109,5	8	19.05	1.
C810*20.0	T-Slot Cutters	HSS	BRIGHT	20.0	100,0	8	20	25,0
C810*22.0	T-Slot Cutters	HSS	BRIGHT	22.0	108,0	8	22	25,0
C810*7/8	T-Slot Cutters	HSS	BRIGHT	7/8	117,5	8	22.23	1.
C810*1	T-Slot Cutters	HSS	BRIGHT	1	127,0	8	25.4	1.