


- threaded barrel, M30 x 1.5
- Chrome-plated brass
- factor 1 for all metals
- magnetic field immune
- extended temperature range
- high switching frequency
- 3-wire DC, 10...30 VDC
- normally open npn output
- connector, M12 x 1

Wiring diagram




Functional principle

Inductive sensors are designed for wear-free and non-contact detection of metal objects. Due to a ferrite-less 3-coil system, uprox factor 1 sensors have distinct advantages. They detect all metals at the same switching distance, are magnetic field immune and feature large switching distances.




Type	Bi10U-M30-AN6X-H1141
Ident-No.	1636150
Rated operating distance Sn	10 mm
Mounting condition	flush
Assured sensing range	$\leq (0,81 \times S_n) \text{ mm}$
Repeatability	$\leq 2 \%$
Temperature drift	$\leq \pm 10 \%$
Hysteresis	$\leq \pm 15 \%$, $\leq -25^\circ\text{C} \vee \geq +70^\circ\text{C}$
Ambient temperature	$-30 \dots +85^\circ\text{C}$
Operating voltage	10... 30VDC
Residual ripple	$\leq 10 \% U_{ss}$
DC rated operational current	$\leq 200 \text{ mA}$
No-load current I_0	$\leq 15 \text{ mA}$
Residual current	$\leq 0.1 \text{ mA}$
Rated insulation voltage	$\leq 0.5 \text{ kV}$
Short-circuit protection	yes / cyclic
Voltage drop at I_e	$\leq 1.8 \text{ V}$
Wire breakage / Reverse polarity protection	yes / complete
Output function	3-wire, normally open, npn
Insulation class	II
Switching frequency	$\leq 2 \text{ kHz}$
Housing	threaded barrel, M30 x 1.5
Dimensions	62 mm
Housing material	metal, CuZn, chrome-plated
Material active face	plastic, PBT
Tightening torque of housing nut	75 Nm
Connection	connectors, M12 x 1
Vibration resistance	55 Hz (1 mm)
Shock resistance	30g (11 ms)
Degree of protection	IP67
Display switch state	LED yellow

Inductive sensor
Bi10U-M30-AN6X-H1141

Mounting instructions		minimum distances
Distance D		2 x B
Distance W		3 x Sn
Distance T		3 x B
Distance S		1,5 x B
Distance G		6 x Sn
Diameter of the active area B		Ø 30 mm



Accessories

Type code	Ident-No.	Short text	Dimension drawing
BST-30B	6947216	fixing clamp with dead-stop; material: PA6	
QM-30	6945103	quick-mount fixing clamp with dead-stop; material: chrome-plated brass male thread M36 x 1.5. Note: The switching distance of proximity switches can be reduced by the use of quick mounting brackets.	
MW-30	6945005	mounting bracket; material: stainless steel A2 1.4301 (AISI 304)	
BSS-30	6901319	fixing clamp; material: polypropylene	