

F

F

E

E

D

D

C

C

B

B

A

A

10

9

8

7

6

5


4

3

2

1

FINISHED LENGTH (SEE TABLE)



CONNECTOR SPECIFICATION:

VOLTAGE RATING	250 VAC/VDC
AMPERAGE RATING	max. 4 AMPS
PROTECTION	IP67
OPERATING TEMPERATURE	-20°C TO 80°C

ITEM	COMPONENT	MATERIAL	FINISH
6	LABLE	MYLAR	BLACK/YELLOW
5	COUPLER	BRASS	NICKEL PLATED
4	PIN CONTACT	COPPER ALLOY	GOLD OVER NICKEL
3	INSERT	PUR	BLACK
2	OVERMOLD	POLYURETHANE (PUR)	YELLOW
1	CABLE- 22/3-5 (COPPER STRANDING) 3/4/5 CONDUCT. 300V	JACKET: PUR	BLACK

MALE FACE VIEW

3-POLE	4-POLE	5-POLE
WIRING DIAGRAM		
1 BROWN 3 BLUE 4 BLACK	1 BROWN 2 WHITE 3 BLUE 4 BLACK	1 BROWN 2 WHITE 3 BLUE 4 BLACK 5 GREY

DESCRIPTION EC NO: WEU2010-0284 DRWN: LSTEMMLE 2010/01/20 CHK'D: NS APPR: NSTAUDIG 2010/01/26	QUALITY SYMBOLS ▽ = 0 ▽ = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE IN/MM		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
			mm	INCH	DRAWN BY DATE		MICRO-CHANGE CORDSET 3/4/5-P. M 90 SE 22/3-5 BLACK PUR CABLE				
		4 PLACES	±---	±---	CHECKED BY DATE						
		3 PLACES	±---	±---	RE 2010/01/21						
		2 PLACES	±---	±.01	APPROVED BY DATE		MOLEX INCORPORATED				
		1 PLACE	±0.3	±---	NSTAUDIG 2010/01/25						
		ANGULAR ± --- °			MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE TABLE SHEET 2		SD-120065-045				1 OF 1		
1	REV				SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

10

9

8

7

6

5

4

3

2

1

	10	9	8	7	6	5	4	3	2	1																																																															
F	<table><tr><th>POL</th><th>MATERIAL NUMBER</th><th>ENGINEERING NUMBER</th><th>FINISHED LENGTH</th></tr><tr><td>3</td><td>1200060288</td><td>803007P03M020</td><td>6.56' +3.5" -0 [2.0M +89 -0]</td></tr></table> <table><tr><th>POL</th><th>MATERIAL NUMBER</th><th>ENGINEERING NUMBER</th><th>FINISHED LENGTH</th></tr><tr><td>4</td><td>1200060592</td><td>804007P03M020</td><td>6.56' +3.5" -0 [2.0M +89 -0]</td></tr><tr><td>4</td><td>1200652145</td><td>804007P03M040</td><td>13.12' +6.5" -0 [4.0M +165 -0]</td></tr><tr><td>4</td><td>1200060594</td><td>804007P03M050</td><td>16.40' +6.5" -0 [5.0M +165 -0]</td></tr><tr><td>4</td><td>1200652146</td><td>804007P03M060</td><td>19.69' +6.5" -0 [6.0M +165 -0]</td></tr><tr><td>4</td><td>1200060595</td><td>804007P03M100</td><td>32.81' +12.5" -0 [10.0M +318 -0]</td></tr></table>										POL	MATERIAL NUMBER	ENGINEERING NUMBER	FINISHED LENGTH	3	1200060288	803007P03M020	6.56' +3.5" -0 [2.0M +89 -0]	POL	MATERIAL NUMBER	ENGINEERING NUMBER	FINISHED LENGTH	4	1200060592	804007P03M020	6.56' +3.5" -0 [2.0M +89 -0]	4	1200652145	804007P03M040	13.12' +6.5" -0 [4.0M +165 -0]	4	1200060594	804007P03M050	16.40' +6.5" -0 [5.0M +165 -0]	4	1200652146	804007P03M060	19.69' +6.5" -0 [6.0M +165 -0]	4	1200060595	804007P03M100	32.81' +12.5" -0 [10.0M +318 -0]	F																														
POL	MATERIAL NUMBER	ENGINEERING NUMBER	FINISHED LENGTH																																																																						
3	1200060288	803007P03M020	6.56' +3.5" -0 [2.0M +89 -0]																																																																						
POL	MATERIAL NUMBER	ENGINEERING NUMBER	FINISHED LENGTH																																																																						
4	1200060592	804007P03M020	6.56' +3.5" -0 [2.0M +89 -0]																																																																						
4	1200652145	804007P03M040	13.12' +6.5" -0 [4.0M +165 -0]																																																																						
4	1200060594	804007P03M050	16.40' +6.5" -0 [5.0M +165 -0]																																																																						
4	1200652146	804007P03M060	19.69' +6.5" -0 [6.0M +165 -0]																																																																						
4	1200060595	804007P03M100	32.81' +12.5" -0 [10.0M +318 -0]																																																																						
E											E																																																														
D											D																																																														
C	<table><tr><th>POL</th><th>MATERIAL NUMBER</th><th>ENGINEERING NUMBER</th><th>FINISHED LENGTH</th></tr><tr><td>5</td><td>1200060697</td><td>805007P03M020</td><td>6.56' +3.5" -0 [2.0M +89 -0]</td></tr><tr><td>5</td><td>1200060699</td><td>805007P03M040</td><td>13.12' +6.5" -0 [4.0M +165 -0]</td></tr><tr><td>5</td><td>1200658186</td><td>805007P03M050</td><td>16.40' +6.5" -0 [5.0M +165 -0]</td></tr><tr><td>5</td><td>1200652149</td><td>805007P03M060</td><td>19.69' +6.5" -0 [6.0M +165 -0]</td></tr><tr><td>5</td><td>1200655006</td><td>805007P03M100</td><td>32.81' +12.5" -0 [10.0M +318 -0]</td></tr></table>										POL	MATERIAL NUMBER	ENGINEERING NUMBER	FINISHED LENGTH	5	1200060697	805007P03M020	6.56' +3.5" -0 [2.0M +89 -0]	5	1200060699	805007P03M040	13.12' +6.5" -0 [4.0M +165 -0]	5	1200658186	805007P03M050	16.40' +6.5" -0 [5.0M +165 -0]	5	1200652149	805007P03M060	19.69' +6.5" -0 [6.0M +165 -0]	5	1200655006	805007P03M100	32.81' +12.5" -0 [10.0M +318 -0]	C																																						
POL	MATERIAL NUMBER	ENGINEERING NUMBER	FINISHED LENGTH																																																																						
5	1200060697	805007P03M020	6.56' +3.5" -0 [2.0M +89 -0]																																																																						
5	1200060699	805007P03M040	13.12' +6.5" -0 [4.0M +165 -0]																																																																						
5	1200658186	805007P03M050	16.40' +6.5" -0 [5.0M +165 -0]																																																																						
5	1200652149	805007P03M060	19.69' +6.5" -0 [6.0M +165 -0]																																																																						
5	1200655006	805007P03M100	32.81' +12.5" -0 [10.0M +318 -0]																																																																						
B											B																																																														
A	<table><tr><td rowspan="5">DESCRIPTION EC NO: WEU2010-0284 DRWN: LSTEMMLE 2010/01/20 CHKD: NS APPR: NSTAUDIG 2010/01/26</td><td rowspan="5">QUALITY SYMBOLS ▽ = 0 ▽C = 0</td><td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE IN/MM</td><td>SCALE 2:1</td><td>DESIGN UNITS METRIC</td><td rowspan="2"> THIRD ANGLE PROJECTION</td></tr><tr><td></td><td>mm</td><td>INCH</td><td>DRAWN BY</td><td>DATE</td><td colspan="2" rowspan="3">MICRO-CHANGE CORDSET 3/4/5-P. M 90 SE 22/3-5 BLACK PUR CABLE</td></tr><tr><td>4 PLACES</td><td>±---</td><td>±---</td><td colspan="2">-----</td></tr><tr><td>3 PLACES</td><td>±---</td><td>±---</td><td colspan="2">CHECKED BY DATE</td></tr><tr><td>2 PLACES</td><td>±---</td><td>±.01</td><td>RE</td><td>2010/01/21</td><td colspan="2" rowspan="2">MOLEX INCORPORATED</td></tr><tr><td>1 PLACE</td><td>±0.3</td><td>±---</td><td colspan="2">APPROVED BY DATE</td></tr><tr><td colspan="3">ANGULAR ± --- °</td><td colspan="2">NSTAUDIG 2010/01/25</td><td colspan="2" rowspan="2">SD-120065-045</td></tr><tr><td colspan="3">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td colspan="2">MATERIAL NO. SEE TABLE</td><td colspan="2">DOCUMENT NO.</td></tr><tr><td>1</td><td>REV</td><td colspan="2"></td><td>SIZE A3</td><td colspan="5">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr></table>										DESCRIPTION EC NO: WEU2010-0284 DRWN: LSTEMMLE 2010/01/20 CHKD: NS APPR: NSTAUDIG 2010/01/26	QUALITY SYMBOLS ▽ = 0 ▽C = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		mm	INCH	DRAWN BY	DATE	MICRO-CHANGE CORDSET 3/4/5-P. M 90 SE 22/3-5 BLACK PUR CABLE		4 PLACES	±---	±---	-----		3 PLACES	±---	±---	CHECKED BY DATE		2 PLACES	±---	±.01	RE	2010/01/21	MOLEX INCORPORATED		1 PLACE	±0.3	±---	APPROVED BY DATE		ANGULAR ± --- °			NSTAUDIG 2010/01/25		SD-120065-045		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO. SEE TABLE		DOCUMENT NO.		1	REV			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					A
DESCRIPTION EC NO: WEU2010-0284 DRWN: LSTEMMLE 2010/01/20 CHKD: NS APPR: NSTAUDIG 2010/01/26	QUALITY SYMBOLS ▽ = 0 ▽C = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION																																																																	
			mm	INCH	DRAWN BY	DATE	MICRO-CHANGE CORDSET 3/4/5-P. M 90 SE 22/3-5 BLACK PUR CABLE																																																																		
		4 PLACES	±---	±---	-----																																																																				
		3 PLACES	±---	±---	CHECKED BY DATE																																																																				
		2 PLACES	±---	±.01	RE	2010/01/21	MOLEX INCORPORATED																																																																		
1 PLACE	±0.3	±---	APPROVED BY DATE																																																																						
ANGULAR ± --- °			NSTAUDIG 2010/01/25		SD-120065-045																																																																				
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO. SEE TABLE				DOCUMENT NO.																																																																		
1	REV			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																				
	10	9	8	7	6	5	4	3	2	1																																																															