


Series E16



Series E16 / Z16 'Easy chain®'

Product Range & Dimensions:



1. High torsional rigidity
2. Small pitch for smooth operation (50 links /m)

Series E16



Technical specifications


Chain type	Weight per link (g)	Weight per metre (kg)
E 16 / Z 16.2	15,5	0,51
E 16 / Z 16.3	17,3	0,57
E 16 / Z 16.4	18,8	0,62
E 16 / Z 16.5	22,7	0,75
E 16 / Z 16.6	25,1	0,83
E 16 / Z 16.7	27,6	0,91

Technical specifications Series E16 / Z16

The following applies to all types listed here:

Material - chain links	igumid NB
Material - mounting brackets*	igumid G
Perm. Temperature °C	-30 / +100
Gliding speed max. m/s	Conditionally suitable
Unsupported V max. m/s	10
Flammability class - chain links	VDE 0304 IIC UL94 V2
Flammability class - mounting brackets*	VDE 0304 IIC UL94HB

*available as igumid NB material on request, please ask us about delivery periods



R	H*	D	K
040**	119	85	210
060	159	110	270
075	189	130	305
100	239	155	395

* The required installation clearance is $HF = H + 15$ mm
(in the case of 0,3 kg/m additional load)
If extremely restricted space is available, please consult us.

** Only Art.No. Z16.3