

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	52		AE1	REVISED PER ECO-11-004917	11MAR11	RK	HMR


- 1

0.00038 MIN SELECTIVE GOLD PLATING ON INSIDE OF RECEPTACLE AND WIRE BARREL OVER NICKEL OVER ALL UNDERPLATE.
- 2


0.00076 MIN SELECTIVE GOLD PLATING ON INSIDE OF RECEPTACLE AND WIRE BARREL OVER NICKEL OVER ALL UNDERPLATE.
- 3

WIRE RANGE: 0.2 – 0.6 MM² (24 – 20 AWG)
- 4


INSULATION RANGE: 1.14 – 1.78




SECTION A-A



SECTION B-B




SECTION C-C



1	0.25 BE CU	60789-8
2	0.25 PH BRZ	60789-3
MATTE TIN	0.25 BE CU	60789-2
PRE-TIN	0.25 PH BRZ	60789-1
FINISH	MATERIAL	PART NUMBER

1.02	.040	1.78	.070	2.54	.100	-	-
0.51	.020	1.486	.0585	2.41	.095	-	-
0.25	.010	1.47	.058	2.24	.088	9.65	.380
0.13	.005	1.40	.055	2.16	.085	3.94	.155
0.00076	.000030	1.359	.0535	1.93	.076	2.92	.115
0.00038	.000015	1.14	.045	1.91	.075	2.79	.110
MM	IN	MM	IN	MM	IN	MM	IN

CONVERSION TABLE



THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN T. BECK 6-11-97	TE Connectivity		
				CHK R. SWING 6-11-97			
				APVD A. BEDDICK 6-17-97	NAME		
				PRODUCT SPEC 108-1025	RECEPTACLE, .058 DIAMETER, 24-20 AWG, .045-.070 INSULATION, LOOSE PIECE, P.C. CONTACT		
				APPLICATION SPEC 114-1008			
				WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C-60789
				CUSTOMER DRAWING	SCALE 10:1	SHEET 1 of 1	REV AE1