

**69830-020LF - Quickie® : PCB Connectors**  
**- Double row - 20 Positions - 2.54 mm (0.1 in.) - Vertical**



[www.fci.com](http://www.fci.com)

## Specifications

### Approvals / Certifications

<b>UL File Number</b>	E66906
<b>Approvals / Certifications</b>	UL and CSA Approved
<b>Dimensional</b>	
<b>Length (Tail)</b>	2.9 mm (0.114 in.)
<b>Electrical</b>	
<b>Current rating</b>	1 amp Continuous
<b>Resistance (Contact)</b>	15 m ohms max.
<b>Resistance (Insulation)</b>	50000 M-ohms
<b>Voltage rating</b>	1000V AC rms
<b>General</b>	
<b>Insulation Displacement Contact (IDC)</b>	PCB Connector
<b>Number of contacts (Total)</b>	20
<b>Number of rows</b>	2
<b>Orientation</b>	Vertical
<b>Termination Style</b>	IDC
<b>Application Equipment</b>	QP-104 QP-112 QP-106
<b>Attachment type (Board)</b>	Through Mount
<b>Mounting</b>	
<b>Solder process</b>	Compatible with Wave and Vapor phase soldering processes low temperature.
<b>Other Features</b>	
<b>Packaging (Type)</b>	Tube
<b>Physical</b>	
<b>Color (Housing)</b>	Blue
<b>Material (Contact)</b>	Phosphor Bronze
<b>Material (Housing)</b>	Glass - Filled Thermoplastic Polyester
<b>Plating (Contact area)</b>	3.81 µm (150 µin.) Tin
<b>Plating (Tail)</b>	3.81 µm min. Tin
<b>Underplating (Contact)</b>	1.27 µm (50 µin.) Nickel
<b>Flammability rating</b>	UL 94 V-0
<b>Temperature (Range)</b>	-65°C to +105°C