

System connectors - FLKM 14-PA/GE/DI - 2290038

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

VARIOFACE front adapter, for GE-FANUC series 90-30, 2 x 8 channels can be connected, digital input




Why buy this product

- Pre-assembled system cables are connected directly to I/O modules using the front adapters



Key commercial data

Packing unit	5 pc
GTIN	 4 017918 057923
Weight per Piece (excluding packing)	41.34 g
Custom tariff number	85366990
Country of origin	Germany

Technical data

General

Nominal voltage U_N	< 50 V AC
	60 V DC
Max. permissible current	1 A (per path)
	3 A (per connection, supply via separate power supply)
Channels which can be connected	16
Connection type, connector	IDC/FLK pin strip (2.54 mm)
Number of connectors	2
No. of positions, connector	14
Number of positions	14
Mounting position	any
Standards/regulations	IEC 60664
	DIN EN 50178
	IEC 62103
Pollution degree	2

System connectors - FLKM 14-PA/GE/DI - 2290038

Technical data

General

Surge voltage category	II
------------------------	----

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Supported controller

Control	GE-FANUC 90-30
- suitable I/O card	IC693 MDL241
	IC693 MDL634
	IC693 MDL645
	IC693 MDL646

Classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242208
eCl@ss 7.0	27242208
eCl@ss 8.0	27242208

ETIM

ETIM 2.0	EC001423
ETIM 3.0	EC001423
ETIM 4.0	EC001423
ETIM 5.0	EC002584

UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

Approvals

Approvals

System connectors - FLKM 14-PA/GE/DI - 2290038

Approvals

Approvals

UL Recognized / cUL Recognized / GOST / cULus Recognized

Ex Approvals

Approvals submitted

Approval details

UL Recognized


cUL Recognized

GOST

cULus Recognized

Drawings

Circuit diagram



Connection scheme FLKM 14-PA/GE/DI