

# Antenna - RAD-ISM-5250-ANT-OMNI-10-N - 5606761

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Directional antenna, enclosure IP65, gain 12 dBi, port N (female)



## Key commercial data

Packing unit	1
GTIN	 4 046356 570978
Custom tariff number	85177019

## Technical data

### Dimensions

Height	419 mm
--------	--------

### Ambient conditions

Degree of protection	IP65
----------------------	------

### General

Frequency range	5.2 GHz
	5.15 GHz ... 5.35 Hz
Horizontal beamwidth	360 °
Vertical beamwidth	8.5 °
Gain	10 dBi
Wind velocity	190 km/h
Connection method	N (female)

## Classifications

### eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	19070102
eCl@ss 5.1	19070102
eCl@ss 6.0	19070102

## Antenna - RAD-ISM-5250-ANT-OMNI-10-N - 5606761

### Classifications

#### eCl@ss

eCl@ss 7.0	19070102
eCl@ss 8.0	19070102

#### ETIM

ETIM 3.0	EC001698
ETIM 4.0	EC001698
ETIM 5.0	EC001698

#### UNSPSC

UNSPSC 6.01	43171611
UNSPSC 7.0901	43221706
UNSPSC 11	43171611
UNSPSC 12.01	43221706
UNSPSC 13.2	43221706