

# 77 32 115 ESD

## Electronics Diagonal Cutter ESD



- for fine cutting work, e.g. in electronics and fine mechanics
- electrically discharging handles - dissipative
- sturdy, zero-backlash box joint
- low-friction double spring for gentle and even opening
- the mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- cutting edges additionally induction hardened, cutting edge hardness approx. 62 HRC
- with two-colour dual component grips, black/grey
- High-grade special tool steel, forged, oil-hardened
- pointed head, with small bevel




### ESD pliers (electrostatic discharge)

electrostatic energy is discharged through the handles in a gradual and controlled manner

which protects components endangered by electrostatic discharge

in accordance with applicable standards, e.g. IEC TR 61 340-5, DIN EN 61 340-5, SP Method 2472

<b>Article No.</b>	77 32 115 ESD
<b>EAN</b>	4003773025122
<b>Head</b>	mirror polished
<b>Handles</b>	with multi-component grips
<b>Style</b>	3
<b>medium hard wire Ø mm</b>	1,0
<b>hard wire Ø mm</b>	0,5
<b>soft wire Ø mm</b>	0,3 - 1,3
<b>B mm</b>	14,0
<b>D mm</b>	7,0
<b>A mm</b>	11,0
<b>Nominal size</b>	115 mm
<b>Length mm</b>	115
<b>Net weight g</b>	79



technical change and errors excepted

