

REZ Series Releasable Ties

Features and Benefits


The unique, patented head design enables quick and simple use. The tie can be inserted in the normal way and pulled tight or the tail can be twisted into the open part of the head and locked into place. The quick-release mechanism can be released by one hand - even when the tie is under tension - by simply pinching the ears.

Application

These releasable and reusable ties are ideal for temporary installations or the addition and/or removal of cables. Suitable for a multitude of uses, such as the packaging industry as a bag closure where access to part of the bag contents may be needed but the bag needs to be re-sealed (example - milk powder in the catering industry).



The REZ ties have a one-hand, simple, release mechanism.



REZ-Series

Material Data	
Material	Polyamide 6.6 (PA66)
Operating Temperature	-40 °C to +85 °C Continuous, (+105 °C for 500 h)
Flammability	UL94 V2



Technical Table

Article-No.	Type	Length (L)	Width (W)	Bundle Ø max.	Min. Tensile Strength (N)	Colour
115-40200	REZ200	200	4.7	50	135	Black (BK)
115-00032	REZ300	305	4.7	80	135	Natural (NA)
115-40300	REZ300	305	4.7	80	135	Black (BK)
115-00043	REZ300	305	4.7	80	135	Red (RD)

All dimensions in mm. Subject to technical changes.


RS1 Series

Features and Benefits

This bobble tie allows a simple and quick fixing.

Application

Ideal for temporary bundling or as a bag closure.



RS1 Series

Material Data	
Material	Polyamide 6.6 (PA66)
Operating Temperature	-40 °C to +85 °C Continuous, (+105 °C for 500 h)
Flammability	UL94 V2



Technical Table

Article-No.	Type	Length (L)	Width (W)	Bundle Ø max.	Colour
111-81100	RS1	110	2.0	31	Black (BK)
111-81103	RS1	110	2.0	31	Natural (NA)

All dimensions in mm. Subject to technical changes.