

**DYMO**

# Facility, Security, and Pro A/V

**Rhino™ 4200**

All-Purpose Labelling Tool with QWERTY Keyboard



## Compact, time-saving labelling for on-the-go pros.

### Print labels 57% faster than the competition.\*

The new DYMO Rhino 4200 gets labelling jobs done fast – and done right. Easily navigate the familiar QWERTY keyboard. Use one-touch “Hot Key” shortcuts to quickly create and format wire/cable wraps, flags, Code 39 and Code 128 barcodes, fixed-length labels, breaker labels and more.

Print labels up to 19mm wide in flexible nylon, permanent polyester and durable vinyl materials – PLUS print directly on heat-shrink tubes. Save even more time with great new features – like the ‘Favourites’ key which provides single-key access to commonly used labels, symbols and terms; and the ‘Custom’ key which eliminates repeated steps by saving customised settings.



Sku No. S0955950



### DYMO | Rhino 4200 features:

- 1 Easy to navigate computer-style QWERTY keyboard**  
Quick and comfortable text entry
- 2 One-Touch “Hot Keys” – a DYMO exclusive**  
Use up to 45.5% fewer keystrokes to create a label than the competition\*\*
- 3 Industrial-strength labelling versatility**  
Print 6mm, 9mm, 12mm and 19mm wide labels in a variety of materials and colours – PLUS print directly on heat-shrink tubes
- 4 NEW “Favourites” key**  
Single-key access to your most commonly used labels, symbols and terms
- 5 NEW “Custom” key prevents needless repetition**  
Customise and save settings for individual label formats













Capable

Up to  
19mm

\* Based on independent testing of Rhino 4200 vs. Brother PT-1400 and Brother PT-7100 in default settings

\*\* Based on independent testing of Rhino 4200 vs. Brother PT-1400 and Brother PT-7100 for wire/cable wrap and flag labels

24mm label widths not for use with the Rhino™ 4200

IND	LABEL APPLICATIONS	LABEL COLOUR	24mm label widths not for use with the Rhino™ 4200				
			6mm	9mm	12mm	19mm	24mm
<b>Labels that stick and stay stuck.</b> DYMO Industrial labels are tough– jobsite tested and UL recognised. Labels won't smear or fade and are built with industrial-strength adhesives to resist moisture, UV light and extreme temperatures. Whether you are labelling to OSHA, ISO and ANSI colour standards or labelling in harsh conditions, DYMO Industrial labels have you covered. DYMO Industrial labels are designed to work with Rhino and LabelManager printers and to perform on a variety of surfaces. <a href="http://www.dymo.com.au">LEARN MORE: www.dymo.com.au</a>	<b>BLACK ON WHITE</b>	-	SD18443	SD18444	SD18445	-	
		<b>WHITE ON BLACK</b>	-	1805437	1805435	1805436	1805432
<b>VINYL</b> - UL Recognised Component to UL969 - RoHS compliant  	Length 5.5m						
<b>PERMANENT POLYESTER</b> - UL Recognised Component to UL969 - RoHS compliant  	Length 5.5m	<b>BLACK ON WHITE</b>	1805442	SD18482	SD18483	SD18484	SD1734523
		<b>BLACK ON CLEAR</b>	1805440	18508DMO	622289	622290	1805433
		<b>BLACK ON METALLIC</b>	-	18485	18486	18487	1805434
<b>HEAT SHRINK TUBE</b> - UL Recognised Component to UL224 - Meets MIL-STD-202G, MIL-M-81531 & SAE-DTL 23053/5 (Class 1 & 3) - RoHS compliant  	Length 1.5m	<b>BLACK ON WHITE</b>	SD18051	SD18053	SD18055	SD18057	-
		<b>BLACK ON YELLOW</b>	18052	18054	18056	18058	-
<b>FLEXIBLE NYLON</b> - UL Recognised Component to UL969 - RoHS compliant  	Length 3.5m	<b>BLACK ON WHITE</b>	-	-	SD18488	SD18489	SD1734524
		<b>BLACK ON YELLOW</b>	-	-	SD18490	SD18491	SD1734525
<b>SELF-LAMINATING</b> - RoHS compliant  	Length 5.5m	<b>BLACK ON WHITE</b>	-	-	-	-	SD1734821

**RHINO 4200**

Code: S0955950  
 Barcode: 3501170955956

**Product specifications:**

- Runs on 6 AA batteries or optional rechargeable lithium-ion battery
- 1 year limited warranty
- Unit weight: 700g
- Units per master carton: 3
- Master carton dimensions (L x W x H) 315 x 305 x 300 mm
- Master carton weight: 2.89kg

**Box includes:**

- Rhino 4200 printer
- Quick Reference Guide
- 12mm white vinyl tape

DYMO, the DYMO logo and Rhino are trademarks or registered trademarks of Newell Rubbermaid. All other trademarks are the property of their respective owners.

**Distributed by:**  
 Newell Australia Pty Ltd  
[www.dymo.com.au](http://www.dymo.com.au)



A **Newell Rubbermaid** Brand