


## Datasheet

# 4.7 $\mu\text{H}$ Ferrite Leaded Inductor, 1.7A Idc

RS Stock number [228-135](#)

Dimensions (inch/mm):



### Description:

RF Inductors consisting of a ferrite based coil former encapsulated in a polypropylene outer case. IDC Max. based on 0.3W dissipation @ 70 °C

### Specification:

- Core Material: Ferrite
- Diameter: 3.3mm
- Dimensions: 3.3 Dia. x 9.14mm
- Inductance: 4.7  $\mu\text{H}$
- Lead Diameter: 0.73mm
- Length: 9.14mm
- Maximum DC Current: 1.7A
- Mounting Type: Axial
- Series: APIE0309