

Marker for terminal blocks - UC-TMF 16 YE - 0819259

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Marker for terminal blocks, Sheet, yellow, unlabeled, can be labeled with: BLUEMARK CLED, BLUEMARK LED, Plotter, Mounting type: Snap into flat marker groove, for terminal block width: 16 mm, Lettering field: 15.45 x 5.1 mm

Why buy this product

- ✓ Labeling service: Phoenix Contact can custom-label all UniCard markers according to your requirements
- ✓ The UC-TMF ... UniCard labeling range includes markers for products with tall and flat marker grooves



Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 151887
Weight per Piece (excluding packing)	7.1 g
Custom tariff number	39269097
Country of origin	Poland
Note	Made to Order (non-returnable)

Technical data

Dimensions

Width (a)	16 mm
-----------	-------

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

General

Color	yellow
Components	free from silicone and halogen
Inflammability class according to UL 94	V2
Material	PA
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	32

Marker for terminal blocks - UC-TMF 16 YE - 0819259

Technical data

General

Number of individual labels per row	4
Marking mounting type	Snap into flat marker groove

Classifications

eCl@ss

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Accessories

Accessories

Magazine

Magazine - P1 UC-MAG 4 - 5146105



Magazine, for CMS-P1-PLOTTER, for accommodating UC-TMF..., UC1-TMF..., UC-WMT...