

## Passive module - VIP-2/SC/FLK50/MODI-TSX/Q - 2322304


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



VARIOFACE interface module, for MODICON® TSX Quantum, with MODICON®-specific labeling, for I/O of 32 channels



### Key commercial data

Packing unit	1 pc
GTIN	 4 046356 451192
Weight per Piece (excluding packing)	220.0 g
Custom tariff number	85369010
Country of origin	United States
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Width	106.1 mm
Height	65.5 mm
Depth	56 mm

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

#### General

Max. permissible operating voltage	60 V AC/DC
Max. perm. current (per branch)	1 A
Number of positions	50
Status display	No
Mounting position	any
Standards/regulations	IEC 60664

## Passive module - VIP-2/SC/FLK50/MODI-TSX/Q - 2322304

### Technical data

#### General

	DIN EN 50178
	IEC 62103
Rated surge voltage	0.6 kV
Pollution degree	2
Surge voltage category	II

#### Connection data for connection 1

Connection name	Field level
Connection method	Screw connection
Conductor cross section solid min.	0.2 mm <sup>2</sup>
Conductor cross section solid max.	4 mm <sup>2</sup>
Conductor cross section stranded min.	0.2 mm <sup>2</sup>
Conductor cross section stranded max.	2.5 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Stripping length	8 mm
Screw thread	M3

#### Connection data for connection 2

Connection name	Controller level
Number of connections	1
Connection method	IDC/FLK pin strip (2.54 mm)
Number of positions	50

#### Supported controller

Controller	Schneider Electric MODICON TSX QUANTUM
- suitable I/O card	DDI 353
	DDI 841
	DDI 853
	DAI 340
	DAI 353
	DAI 440
	DAI 453
	DDO 353
	DDM 390
	ACI 030
	ACI 040
	ATI 030
	ARI 030
	AVI 030
	ACO 020
	ACO 130

# Passive module - VIP-2/SC/FLK50/MODI-TSX/Q - 2322304

## Technical data

### Supported controller

	AVO 020
	EHC 105
	EHC 202

## Classifications

### eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242608
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152

### ETIM


ETIM 2.0	EC001434
ETIM 3.0	EC001604
ETIM 4.0	EC001604
ETIM 5.0	EC002780

### UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

## Drawings

Circuit diagram



Connection scheme VIP-2/.../FLK50/MODI-TSX/Q

