


## Tool Specification

1. Part Number: YRS-859

2. Terminal: SSH-003T-P0.2/SSHL-003T-P0.2

3. Application

| Crimp Position | Wire Size     | Tensile Strength N (kgf) | Strip Length mm |
|----------------|---------------|--------------------------|-----------------|
| 30             | UL1571 AWG 30 | 5(0.5) min.              | 1.5             |
| 28             | UL1571 AWG 28 | 10(1.0) min.             | 1.5             |



## Upper Crimp Die

- Check the crimp appearance and tensile strength prior to use.
- Select the appropriate crimp position based on the wire size that will be used.
- The insulation barrel is set for type of wire listed and is not adjustable.