

Sa Shp-T 150w Basic Plus E40

20847156



Range features

PRODUCT OVERVIEW

Ordering number	20847156
Technology	HID
Average life (Rated) (h)	32000
Energy class	A+
Dimmable	No
Type	SHP-T
EAN code	5410288208473
CRI (Ra)	20
Colour temperature (K)	2000
Luminous flux (Rated) (lm)	17000
Efficacy (Rated) (lm/w)	112
Watt (Nominal) (W)	150

Sa Shp-T 150w Basic Plus E40

20847156

DATA TABLE

General data

Technology	HID
Ordering number	20847156
Average life (Nominal) (h)	32000
Average life (Rated) (h)	32000
Energy class	A+
Dimmable	No
Type	SHP-T
EAN code	5410288208473
Long description	
Product name	Sa Shp-T 150w Basic Plus E40
Lamp mercury content (mg)	8
IEC Reference	IEC 60662
IEC Reference 2	IEC 62035
Rated survival factor at 2000 h 50Hz	1
Rated survival factor at 4000 h 50Hz	0.99
Rated survival factor at 6000 h 50Hz	0.98
Rated survival factor at 8000 h 50Hz	0.97
Rated survival factor at 12000 h 50Hz	0.93
Rated survival factor at 16000 h 50Hz	0.9
Rated survival factor at 20000 h 50Hz	0.86

Optical data

CRI (Ra)	20
Colour temperature (K)	2000
Luminous flux (Rated) (lm)	17000
Luminous flux (Nominal) (lm)	17000
Ambient temperature for maximum luminous flux (°C)	25
Rated lumen maint. factor at 2000 h 50Hz	0.97
Rated lumen maint. factor at 4000 h 50Hz	0.96
Rated lumen maint. factor at 6000 h 50Hz	0.95
Rated lumen maint. factor at 8000 h 50Hz	0.93
Rated lumen maint. factor at 12000 h 50Hz	0.9
Rated lumen maint. factor at 16000 h 50Hz	0.88
Rated lumen maint. factor at 20000 h 50Hz	0.86

Sa Shp-T 150w Basic Plus E40

20847156

Electrical data

kWh per 1000 hours burning time	165
Efficacy (Rated) (lm/w)	112
Watt (Rated) (W)	150
Watt (Nominal) (W)	150

Physical data

Lamp Length (mm) - C/L	210
Max. Lamp Diameter (mm) - D	47

ENERGY LABEL

