



Roller lever, metal

Part no.
Article no.
Catalog No.

LSM-XL
266156
LSM-XL



Powering Business Worldwide™

Delivery programme

Basic function		Operating heads
Part group reference		LS(M)-...
Product range		Roller lever
Design		EN 50047 Form E
Description		Long
For use with		Basic devices LS(M)...
Notes The operating head can be rotated at 90° intervals to adapt to the specified approach direction.		

Approvals

Product Standards
UL File No.
UL Category Control No.
CSA File No.
CSA Class No.
North America Certification

IEC/EN 60947-5; UL 508; CSA-C22.2 No. 14; CE marking
E29184
NKCR
12528
3211-03
UL listed, CSA certified

Technical data ETIM 5.0

Sensors (EG000026) / Drive head for position switches/hinge switches (EC001483)	
Electric engineering, automation, process control engineering / Binary sensor technology, safety-related sensor technology / Position switch / Drive head for position switches (ecl@ss8-27-27-06-04 [BAA083008])	
Type of control element	Roller lever

Dimensions

