







.040	1.02		
.035	0.89		
.032	0.81		
.025	0.64	1.000	25.40
.020	0.51	.535	13.59
.015	0.38	.310	7.87
.010	0.25	.295	7.49
.008	0.20	.260	6.60
.005	0.13	.225	5.72
.001	0.03	.140	3.56
.000350	0.00889	.130	3.30
.000150	0.00381	.125	3.18
.000050	0.00127	.100	2.54
.000030	0.00076	.063	1.60
.000	0.00	.050	1.27
IN	MM	IN	MM

CONVERSION TABLE

RECOMMENDED MOUNTING HOLE PATTERN
FOR .063 THICK P.C. BOARD

13 15	2.800	71.12	28	5-641215-8
	2.700	68.58	27	5-641215-7
	2.600	66.04	26	5-641215-6
	2.500	63.50	25	5-641215-5
	2.400	60.96	24	5-641215-4
	2.300	58.42	23	5-641215-3
	2.200	55.88	22	5-641215-2
	2.100	53.34	21	5-641215-1
	2.000	50.80	20	5-641215-0
	1.900	48.26	19	4-641215-9
	1.800	45.72	18	4-641215-8
	1.700	43.18	17	4-641215-7
	1.600	40.64	16	4-641215-6
	1.500	38.10	15	4-641215-5
	1.400	35.56	14	4-641215-4
	1.300	33.02	13	4-641215-3
	1.200	30.48	12	4-641215-2
	1.100	27.94	11	4-641215-1
	1.000	25.40	10	4-641215-0
	.900	22.86	9	3-641215-9
.800	20.32	8	3-641215-8	
.700	17.78	7	3-641215-7	
.600	15.24	6	3-641215-6	
.500	12.70	5	3-641215-5	
.400	10.16	4	3-641215-4	
.300	7.62	3	3-641215-3	
.200	5.08	2	3-641215-2	
	IN	MM	NO OF POSITIONS	PART NUMBER
	L			

13	14	16	SUP BY 5-641215-8	2.800	71.12	28	2-641215-8
		16	SUP BY 5-641215-7	2.700	68.58	27	2-641215-7
		16	SUP BY 5-641215-6	2.600	66.04	26	2-641215-6
		16	SUP BY 5-641215-5	2.500	63.50	25	2-641215-5
				2.400	60.96	24	2-641215-4
		16	SUP BY 5-641215-3	2.300	58.42	23	2-641215-3
		16	SUP BY 5-641215-2	2.200	55.88	22	2-641215-2
		16	SUP BY 5-641215-1	2.100	53.34	21	2-641215-1
				2.000	50.80	20	2-641215-0
		16	SUP BY 4-641215-9	1.900	48.26	19	1-641215-9
				1.800	45.72	18	1-641215-8
				1.700	43.18	17	1-641215-7
				1.600	40.64	16	1-641215-6
				1.500	38.10	15	1-641215-5
				1.400	35.56	14	1-641215-4
				1.300	33.02	13	1-641215-3
				1.200	30.48	12	1-641215-2
				1.100	27.94	11	1-641215-1
				1.000	25.40	10	1-641215-0
				.900	22.86	9	641215-9
				.800	20.32	8	641215-8
				.700	17.78	7	641215-7
				.600	15.24	6	641215-6
				.500	12.70	5	641215-5
				.400	10.16	4	641215-4
				.300	7.62	3	641215-3
				.200	5.08	2	641215-2
			IN MM			NO OF POSITIONS	PART NUMBER
			L				

- ① POST TO WITHSTAND 13 NEWTONS (3 LBS) MIN. AXIAL FORCE IN BOTH DIRECTIONS SHOWN WITHOUT DISLODGING.
- ② TOLERANCES APPLY TO SOLDER SIDE OF BOARD.
- ③ MEASURED AT SURFACE -A-
- ④ PLASTIC FLASH PERMITTED IN THIS AREA.
5. PARTS COMPLY WITH AMP SOLDERABILITY SPEC. NO. 109-11-2.
- ⑥ ONE HOLE MAY BE UNDERSIZED(.032-.035 DIA) FOR ASSEMBLY RETENTION DURING WAVE SOLDERING.
- ⑦ MATERIAL: HEADER-THERMOPLASTIC POLYESTER
UL94V-0(NATURAL)
POST-COPPER ALLOY (SEE NOTES
13 & 14 FOR PLATING)
- ⑧ COORDINATE DIMENSION APPLIES FROM CENTER OF ACTUAL FEATURE.
9. PLASTIC BURRS CAUSED BY CUT-OFF TOOLING ARE PERMITTED WITHIN THE MAXIMUM TOLERANCE ENVELOPE.
- ⑩ POSTS TO BE MEASURED WHEN STRIP IS HELD FLAT.
- ⑪ POSTS MUSTS WITHSTAND TWO 90° BENDS AGAINST EXTRUSION WITHOUT BREAKING.
- ⑫ DIMENSION SHOULD BE .130 MIN WHEN MATING WITH A MTA 100 CONNECTOR ASSEMBLY OR A CST 100 CONNECTOR.
- ⑬ GOLD PLATE AREA,.000030 MIN.,ALL SIDES,OVER NICKEL UNDERPLATE,.000050 MIN.,ALL SIDES AND ENTIRE LENGTH OF POST.
- ⑭ BRIGHT TIN/LEAD (93/7) PLATE AREA,.000150-.000350 THICK,ALL FOUR SIDES,.140 MIN.
- ⑮ TIN PLATE AREA,.000150-.000350 THICK,ALL FOUR SIDES,.140 MIN.
- ⑯ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN K. WHITAKER CHK D. BOSSI		11JUN04 11JUN04		 TE Connectivity	
DIMENSIONS:		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME		MTA-100 HEADER ASSEMBLY, FRICTION LOCK, NOTCHED, .025 SQUARE STRAIGHT POST, .000030 GOLD PLATED	
INCHES		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± '0.30'		APVD D. BOSSI 11JUN04 PRODUCT SPEC — APPLICATION SPEC —		SIZE A1	
				CAGE CODE 00779		DRAWING NO C-641215	
MATERIAL		FINISH		WEIGHT —		RESTRICTED TO —	
				CUSTOMER DRAWING		SCALE 8:1	
						SHEET 1 OF 1	
						REV W2	