




STRAIGHT PATTERN SNIPS

PART NO.	SIZE INCH	L MM	a MM	b MM			G.W. (kg)
93302	8"	205.0	30	87	8	48	17.4
93303	10"	254.0	35	105	6	36	18.9
93304	12"	305.0	40	110	6	24	17.0
93305	14"	355.0	45	110	6	24	22.0
93306	16"	425.0	60	145	0	12	22.5



ANSI B107.16

- Snips are hot drop forged from the finest steel (on-piece construction)
- Cutting edges induction hardened to HRC 58-60
- Bulldog pattern snips for trimming extra heavy stock cuts up to 1.6mm cold rolled steel or 1.0mm AISI-304 stainless steel


⚠ Nature of this product is subject to wear and tear upon usage. Not covered under Lifetime Warranty.




BOLT CUTTER

PART NO.	SIZE INCH	L MM	a MM	b MM			G.W. (kg)
93501	8"	212.5	41	63.5	6	60	19.6

⚠ Nature of this product is subject to wear and tear upon usage. Not covered under Lifetime Warranty.




BOLT CUTTER



PART NO.	SIZE INCH	L MM	a MM	b MM	Cutting Capacity Ømm		G.W. (kg)
93502	12"	325.0	54	120	5	20	16.4
93503	14"	365.0	60	134	7	20	20.9
93504	18"	498.0	71	143	8	20	32.5
93505	24"	655.0	85	151	10	10	27.6
93506	30"	810.0	95	160	13	6	26.9
93507	36"	980.0	110	190	15	5	33.0
93508	42"					3	26.0
93509	48"					2	26.0

- Loosen nuts on cam bolts about one round (360°)
- Align cutter jaws by rotating the cam bolt move arrows on cam bolt inward to close jaw tighten nuts

⚠ Do not cut over HRC 40° metal & exceed the cutting capacity of the tool. Do not twist or pry with tool while cutting. Nature of this product is subject to wear and tear upon usage. Not covered under Lifetime Warranty.



TUBING CUTTER



PART NO.	SIZE MM			G.W. (kg)
97301	3-28	5	40	13.7
97302	3-32	4	32	10.0

- For copper, brass, or aluminum tubing and thin-wall conduit

⚠ Nature of this product is subject to wear and tear upon usage. Not covered under Lifetime Warranty.



TUBING CUTTER


PART NO.	SIZE MM			G.W. (kg)
97303	6-64	2	12	9.2

- For copper, brass, or aluminum tubing and thin-wall conduit

⚠ Nature of this product is subject to wear and tear upon usage. Not covered under Lifetime Warranty.



PVC TUBING CUTTER



PART NO.	SIZE MM			G.W. (kg)
97304	3-42	3	18	6.8

- All-metal construction for greater durability
- Handle locks for safety

⚠ Nature of this product is subject to wear and tear upon usage. Not covered under Lifetime Warranty.



MINI TUBING CUTTER



PART NO.	SIZE MM			G.W. (kg)
97305	3-16	12	48	6.8

- For cutting copper, aluminum, brass and thin wall tubing
- Large knob for greater torque

⚠ Nature of this product is subject to wear and tear upon usage. Not covered under Lifetime Warranty.



2PC SPARE BLADE



PART NO.	SIZE MM			G.W. (kg)
97311	3.0x18	12	240	8.8

- Spare blade for 97301 and 97302 tubing cutter

⚠ Nature of this product is subject to wear and tear upon usage. Not covered under Lifetime Warranty.



2PC SPARE BLADE

PART NO.	SIZE MM			G.W. (kg)
97312	6.2x18 6.2x22	12	240	8.8

- Spare blade for 97303 tubing cutter

⚠ Nature of this product is subject to wear and tear upon usage. Not covered under Lifetime Warranty.

