






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		B3	REVISED PER ECO-11-004587	11MAR11	RK	HMR

SPECIFICATIONS:

MATERIAL:

CASE: PBT 30% GLASS UL94V-O
TERMINAL: COPPER ALLOY, TIN OVER NICKEL PLATE

- 1 ALL MATERIALS AND FINISHES SHALL COMPLY WITH EU DIRECTIVE 2002/95/EC OF 27JAN2003 (ROHS)
- 2 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED BOARD LAYOUT

2 OBSOLETE	30.48 [1.200]	12	1-1825190-0
	25.40 [1.000]	10	1825190-9
	22.86 [.900]	9	1825190-8
	20.32 [.800]	8	1825190-7
	17.78 [.700]	7	1825190-6
	15.24 [.600]	6	1825190-5
2 OBSOLETE	12.70 [.500]	5	1825190-4
	10.16 [.400]	4	1825190-3
	7.62 [.300]	3	1825190-2
2 OBSOLETE	2.54 [.200]	2	1825190-1
	DIM A	POSITION	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B.S.VISWESWARA 06MAY05	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK M.S.SARVER				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M.S.SARVER	NAME SHUNT, DIP, PROGRAMMABLE		
	0 PLC ± -		PRODUCT SPEC			
	1 PLC ± -		APPLICATION SPEC	SIZE A2		
	2 PLC ± 0.03[.001]			CAGE CODE 00779		
MATERIAL SEE TABLE		FINISH -	WEIGHT -	DRAWING NO C=1825190		RESTRICTED TO -
CUSTOMER DRAWING			SCALE 4:1	SHEET 1 OF 1	REV B3	