

ULTRASONIC CLEANING LIQUID #745-7494

Chemwatch Independent Material Safety Data Sheet
Issue Date: 10-Jan-2013
9317SP

CHEMWATCH 4764-48
Version No:2.1.1.1
CD 2012/4 Page 1 of 7

Section 1 - CHEMICAL PRODUCT AND COMPANY IDENTIFICATION

PRODUCT NAME

ULTRASONIC CLEANING LIQUID #745-7494

SYNONYMS

"Manufacturer's Code: 745-7494"

PRODUCT USE

Cleaners - Precision.

SUPPLIER

Company: RS Components Pty Ltd
Address:
Units 30 & 31, 761 Great South Road
Penrose
Auckland, 1006
New Zealand
Telephone: +64 9 526 1600
Fax: +64 9 579 1700

Company: RS Components Pty Ltd
Address:
25 Pavesi Street
Smithfield
NSW, 2164
Australia
Telephone: +1 300 656 636
Emergency Tel: 1800 039 008 (24 hours)
Emergency Tel: +61 3 9573 3112
Fax: +1 300 656 696

Section 2 - HAZARDS IDENTIFICATION

STATEMENT OF HAZARDOUS NATURE

HAZARDOUS SUBSTANCE. NON-DANGEROUS GOODS. According to the Criteria of NOHSC, and the ADG Code.



RISK

■ Irritating to eyes and skin.

SAFETY

- Avoid contact with skin.
- Avoid contact with eyes.
- Wear suitable gloves.
- Wear eye/face protection.
- To clean the floor and all objects contaminated by this material, use water.
- In case of contact with eyes, rinse with plenty of water and contact Doctor or Poisons Information Centre.
- If swallowed, IMMEDIATELY contact Doctor or Poisons Information Centre. (show this container or label).

Section 3 - COMPOSITION / INFORMATION ON INGREDIENTS

NAME	CAS RN	%
propylene glycol monomethyl ether - alpha isomer	107-98-2	1-5
sodium metasilicate, anhydrous	6834-92-0	1-5
ethanolamine	141-43-5	0-1
water	7732-18-5	>60

Section 4 - FIRST AID MEASURES

SWALLOWED

- Immediately give a glass of water.

continued...

ULTRASONIC CLEANING LIQUID #745-7494

Chemwatch Independent Material Safety Data Sheet

Issue Date: 10-Jan-2013

9317SP

CHEMWATCH 4764-48

Version No:2.1.1.1

CD 2012/4 Page 2 of 7

Section 4 - FIRST AID MEASURES

- First aid is not generally required. If in doubt, contact a Poisons Information Centre or a doctor.

EYE

- If this product comes in contact with the eyes:
 - Wash out immediately with fresh running water.
 - Ensure complete irrigation of the eye by keeping eyelids apart and away from eye and moving the eyelids by occasionally lifting the upper and lower lids.
 - Seek medical attention without delay; if pain persists or recurs seek medical attention.
 - Removal of contact lenses after an eye injury should only be undertaken by skilled personnel.

SKIN

- If skin contact occurs:
 - Immediately remove all contaminated clothing, including footwear.
 - Flush skin and hair with running water (and soap if available).
 - Seek medical attention in event of irritation.

INHALED

- If fumes, aerosols or combustion products are inhaled remove from contaminated area.
- Other measures are usually unnecessary.

NOTES TO PHYSICIAN

- Treat symptomatically.

Section 5 - FIRE FIGHTING MEASURES

EXTINGUISHING MEDIA

- The product contains a substantial proportion of water, therefore there are no restrictions on the type of extinguishing media which may be used. Choice of extinguishing media should take into account surrounding areas. Though the material is non-combustible, evaporation of water from the mixture, caused by the heat of nearby fire, may produce floating layers of combustible substances. In such an event consider:
 - foam.

FIRE FIGHTING

- Alert Fire Brigade and tell them location and nature of hazard.
- Wear breathing apparatus plus protective gloves in the event of a fire.
- Prevent, by any means available, spillage from entering drains or water courses.
- Use fire fighting procedures suitable for surrounding area.

FIRE/EXPLOSION HAZARD

- The material is not readily combustible under normal conditions.
 - However, it will break down under fire conditions and the organic component may burn.
 - Not considered to be a significant fire risk.
 - Heat may cause expansion or decomposition with violent rupture of containers.
- Decomposes on heating and produces toxic fumes of: carbon dioxide (CO₂), other pyrolysis products typical of burning organic material.
- May emit poisonous fumes.
- May emit corrosive fumes.

FIRE INCOMPATIBILITY

- None known.

HAZCHEM

None

Section 6 - ACCIDENTAL RELEASE MEASURES

MINOR SPILLS

- Clean up all spills immediately.
- Avoid breathing vapours and contact with skin and eyes.
- Control personal contact with the substance, by using protective equipment.
- Contain and absorb spill with sand, earth, inert material or vermiculite.

MAJOR SPILLS

- Moderate hazard.
 - Clear area of personnel and move upwind.
 - Alert Fire Brigade and tell them location and nature of hazard.

continued...

ULTRASONIC CLEANING LIQUID #745-7494

Chemwatch Independent Material Safety Data Sheet
Issue Date: 10-Jan-2013
9317SP

CHEMWATCH 4764-48
Version No:2.1.1.1
CD 2012/4 Page 3 of 7

Section 6 - ACCIDENTAL RELEASE MEASURES

- Wear breathing apparatus plus protective gloves.
- Prevent, by any means available, spillage from entering drains or water course.

Personal Protective Equipment advice is contained in Section 8 of the MSDS.

Section 7 - HANDLING AND STORAGE

PROCEDURE FOR HANDLING

- DO NOT allow clothing wet with material to stay in contact with skin.
- Avoid all personal contact, including inhalation.
- Wear protective clothing when risk of exposure occurs.
- Use in a well-ventilated area.
- Prevent concentration in hollows and sumps.

SUITABLE CONTAINER

- Polyethylene or polypropylene container.
- Packing as recommended by manufacturer.
- Check all containers are clearly labelled and free from leaks.

STORAGE INCOMPATIBILITY

- Avoid reaction with oxidising agents.

STORAGE REQUIREMENTS

- Store in original containers.
- Keep containers securely sealed.
- Store in a cool, dry, well-ventilated area.
- Store away from incompatible materials and foodstuff containers.

Section 8 - EXPOSURE CONTROLS / PERSONAL PROTECTION

EXPOSURE CONTROLS

Source	Material	TWA ppm	TWA mg/m ³	STEL ppm	STEL mg/m ³
Australia Exposure Standards	propylene glycol monomethyl ether - alpha isomer (Propylene glycol monomethyl ether)	100	369	150	553
Australia Exposure Standards	ethanolamine (Ethanolamine)	3	7.5	6	15

The following materials had no OELs on our records

- sodium metasilicate, anhydrous:
- water:

CAS:6834- 92- 0
CAS:7732- 18- 5

MATERIAL DATA

ETHANOLAMINE:

ULTRASONIC CLEANING LIQUID #745-7494:

- for monoethanolamine:

Odour threshold: 3-4 ppm.

Continuous exposure at 5 ppm produced only slight systemic effects. the longer retained, the greater the toxicity,.

PROPYLENE GLYCOL MONOMETHYL ETHER - ALPHA ISOMER:

ULTRASONIC CLEANING LIQUID #745-7494:

- for propylene glycol monomethyl ether (PGME)

Odour Threshold: 10 ppm.

The TLV-TWA is protective against discomfort caused by odour, against eye and skin irritation, and chronic effects (including possible liver and kidney damage).<</>.

SODIUM METASILICATE, ANHYDROUS:

- Sensory irritants are chemicals that produce temporary and undesirable side-effects on the eyes, nose or throat.

Historically occupational exposure standards for these irritants have been based on observation of workers' responses to various airborne concentrations.

No specific exposure limits have been established for soluble silicates.

continued...

ULTRASONIC CLEANING LIQUID #745-7494

Chemwatch Independent Material Safety Data Sheet
Issue Date: 10-Jan-2013
9317SP

CHEMWATCH 4764-48
Version No:2.1.1.1
CD 2012/4 Page 4 of 7

Section 8 - EXPOSURE CONTROLS / PERSONAL PROTECTION

For liquids the creation of aerosols should be avoided.
CEL TWA: 2 mg/m³

[Manufacturer]

WATER:

- No exposure limits set by NOHSC or ACGIH.

PERSONAL PROTECTION

RESPIRATOR

- Type A Filter of sufficient capacity. (AS/NZS 1716 & 1715, EN 143:2000 & 149:2001, ANSI Z88 or national equivalent)

EYE

- Safety glasses with side shields.
- Chemical goggles.
- Contact lenses may pose a special hazard; soft contact lenses may absorb and concentrate irritants. A written policy document, describing the wearing of lens or restrictions on use, should be created for each workplace or task. This should include a review of lens absorption and adsorption for the class of chemicals in use and an account of injury experience. Medical and first-aid personnel should be trained in their removal and suitable equipment should be readily available. In the event of chemical exposure, begin eye irrigation immediately and remove contact lens as soon as practicable. Lens should be removed at the first signs of eye redness or irritation - lens should be removed in a clean environment only after workers have washed hands thoroughly. [CDC NIOSH Current Intelligence Bulletin 59], [AS/NZS 1336 or national equivalent].

HANDS/FEET

- Wear chemical protective gloves, e.g. PVC.
- Wear safety footwear or safety gumboots, e.g. Rubber.

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality which vary from manufacturer to manufacturer. Where the chemical is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

The exact break through time for substances has to be obtained from the manufacturer of the protective gloves and has to be observed when making a final choice.

Suitability and durability of glove type is dependent on usage. Important factors in the selection of gloves include:

OTHER

- Overalls.
- P.V.C. apron.
- Barrier cream.
- Skin cleansing cream.

ENGINEERING CONTROLS

- Engineering controls are used to remove a hazard or place a barrier between the worker and the hazard. Well-designed engineering controls can be highly effective in protecting workers and will typically be independent of worker interactions to provide this high level of protection.

The basic types of engineering controls are:

Process controls which involve changing the way a job activity or process is done to reduce the risk.

Enclosure and/or isolation of emission source which keeps a selected hazard "physically" away from the worker and ventilation that strategically "adds" and "removes" air in the work environment.

Section 9 - PHYSICAL AND CHEMICAL PROPERTIES

APPEARANCE

Colourless highly alkaline liquid with a characteristic odour; mixes with water.

PHYSICAL PROPERTIES

Liquid.
Mixes with water.

State	Liquid	Molecular Weight	Not Applicable
Melting Range (°C)	Not Available	Viscosity	Not Available
Boiling Range (°C)	Not Available	Solubility in water (g/L)	Miscible
Flash Point (°C)	Not Applicable	pH (1% solution)	Not Available
Decomposition Temp (°C)	Not Available	pH (as supplied)	13.5
Autoignition Temp (°C)	Not Available	Vapour Pressure (kPa)	Not Available
Upper Explosive Limit (%)	Not Available	Specific Gravity (water=1)	1.025 @ 20 deg.C
Lower Explosive Limit (%)	Not Available	Relative Vapour Density (air=1)	Not Available
Volatile Component (%vol)	Not Available	Evaporation Rate	Not Available

continued...

ULTRASONIC CLEANING LIQUID #745-7494

Chemwatch Independent Material Safety Data Sheet
Issue Date: 10-Jan-2013
9317SP

CHEMWATCH 4764-48
Version No:2.1.1.1
CD 2012/4 Page 5 of 7

Section 10 - STABILITY AND REACTIVITY

CONDITIONS CONTRIBUTING TO INSTABILITY

- Presence of incompatible materials.
 - Product is considered stable.
 - Hazardous polymerisation will not occur.
- For incompatible materials - refer to Section 7 - Handling and Storage.*

Section 11 - TOXICOLOGICAL INFORMATION

POTENTIAL HEALTH EFFECTS

ACUTE HEALTH EFFECTS

SWALLOWED

■ The material has NOT been classified by EC Directives or other classification systems as "harmful by ingestion". This is because of the lack of corroborating animal or human evidence. The material may still be damaging to the health of the individual, following ingestion, especially where pre-existing organ (eg. liver, kidney) damage is evident. Present definitions of harmful or toxic substances are generally based on doses producing mortality rather than those producing morbidity (disease, ill-health). Gastrointestinal tract discomfort may produce nausea and vomiting. In an occupational setting however, ingestion of insignificant quantities is not thought to be cause for concern.

EYE

■ This material can cause eye irritation and damage in some persons.

SKIN

■ This material can cause inflammation of the skin oncontact in some persons.
The material may accentuate any pre-existing dermatitis condition.
Open cuts, abraded or irritated skin should not be exposed to this material.
Entry into the blood-stream, through, for example, cuts, abrasions or lesions, may produce systemic injury with harmful effects.
Examine the skin prior to the use of the material and ensure that any external damage is suitably protected.

INHALED

■ The material is not thought to produce adverse health effects or irritation of the respiratory tract (as classified by EC Directives using animal models). Nevertheless, good hygiene practice requires that exposure be kept to a minimum and that suitable control measures be used in an occupational setting.
Not normally a hazard due to non-volatile nature of product.

CHRONIC HEALTH EFFECTS

■ Substance accumulation, in the human body, may occur and may cause some concern following repeated or long-term occupational exposure.

TOXICITY AND IRRITATION

■ No significant acute toxicological data identified in literature search.
for propylene glycol ethers (PGEs):
Typical propylene glycol ethers include propylene glycol n-butyl ether (PnB); dipropylene glycol n-butyl ether (DPnB); dipropylene glycol methyl ether acetate (DPMA); tripropylene glycol methyl ether (TPM).
Testing of a wide variety of propylene glycol ethers Testing of a wide variety of propylene glycol ethers has shown that propylene glycol-based ethers are less toxic than some ethers of the ethylene series.

SKIN

propylene glycol monomethyl ether - alpha isomer	GESAMP/EHS Composite List - GESAMP Hazard Profiles	D1: skin irritation/corrosion	2
ethanolamine	GESAMP/EHS Composite List - GESAMP Hazard Profiles	D1: skin irritation/corrosion	3A

Section 12 - ECOLOGICAL INFORMATION

No data

Ecotoxicity

continued...

ULTRASONIC CLEANING LIQUID #745-7494

Chemwatch Independent Material Safety Data Sheet

Issue Date: 10-Jan-2013

9317SP

CHEMWATCH 4764-48

Version No:2.1.1.1

CD 2012/4 Page 6 of 7

Section 12 - ECOLOGICAL INFORMATION

Ingredient	Persistence: Water/Soil	Persistence: Air	Bioaccumulation	Mobility
propylene glycol monomethyl ether - alpha isomer	LOW	LOW	LOW	HIGH
sodium metasilicate, anhydrous	No Data Available	No Data Available	No Data Available	No Data Available
ethanolamine	LOW	No Data Available	LOW	HIGH

Section 13 - DISPOSAL CONSIDERATIONS

■ Legislation addressing waste disposal requirements may differ by country, state and/ or territory. Each user must refer to laws operating in their area.

A Hierarchy of Controls seems to be common - the user should investigate:

- Reduction.
- DO NOT allow wash water from cleaning or process equipment to enter drains.
- It may be necessary to collect all wash water for treatment before disposal.
- In all cases disposal to sewer may be subject to local laws and regulations and these should be considered first.
- Where in doubt contact the responsible authority.
- Recycle wherever possible.
- Consult manufacturer for recycling options or consult local or regional waste management authority for disposal if no suitable treatment or disposal facility can be identified.
- Dispose of by: burial in a land-fill specifically licenced to accept chemical and / or pharmaceutical wastes or incineration in a licenced apparatus (after admixture with suitable combustible material).
- Decontaminate empty containers. Observe all label safeguards until containers are cleaned and destroyed.

Section 14 - TRANSPORTATION INFORMATION

HAZCHEM:

None (ADG7)

NOT REGULATED FOR TRANSPORT OF DANGEROUS GOODS: ADG7, UN, IATA, IMDG

Section 15 - REGULATORY INFORMATION

Indications of Danger:

Xi Irritant

POISONS SCHEDULE None

REGULATIONS

Regulations for ingredients

propylene glycol monomethyl ether - alpha isomer (CAS: 107-98-2) is found on the following regulatory lists;

"Australia - South Australia Controlled Substances (Poisons) Regulations - Schedule E: Schedule 2 poisons authorised to be sold by holder of a medicine sellers licence", "Australia Exposure Standards", "Australia Hazardous Substances", "Australia Inventory of Chemical Substances (AICS)", "Australia National Pollutant Inventory", "FisherTransport Information", "GESAMP/EHS Composite List - GESAMP Hazard Profiles", "IMO IBC Code Chapter 17: Summary of minimum requirements", "IMO MARPOL 73/78 (Annex II) - List of Noxious Liquid Substances Carried in Bulk", "International Chemical Secretariat (ChemSec) SIN List (*Substitute It Now!)", "International Council of Chemical Associations (ICCA) - High Production Volume List", "International Fragrance Association (IFRA) Survey: Transparency List", "OECD List of High Production Volume (HPV) Chemicals", "OSPAR National List of Candidates for Substitution - Norway"

sodium metasilicate, anhydrous (CAS: 6834-92-0) is found on the following regulatory lists;

"Australia Hazardous Substances", "Australia Inventory of Chemical Substances (AICS)", "Australia Standard for the Uniform Scheduling of Medicines and Poisons (SUSMP) - Appendix C", "Australia Standard for the Uniform Scheduling of Medicines and Poisons (SUSMP) - Appendix E (Part 2)", "Australia Standard for the Uniform Scheduling of Medicines and Poisons (SUSMP) - Appendix F (Part 3)", "Australia Standard for the Uniform Scheduling of Medicines and Poisons (SUSMP) - Schedule 5", "Australia Standard for the Uniform Scheduling of Medicines and Poisons (SUSMP) - Schedule 6", "FisherTransport Information", "International Council of Chemical Associations (ICCA) - High Production Volume List", "OECD List of High Production Volume (HPV) Chemicals"

continued...

ULTRASONIC CLEANING LIQUID #745-7494

Chemwatch Independent Material Safety Data Sheet

Issue Date: 10-Jan-2013

9317SP

CHEMWATCH 4764-48

Version No:2.1.1.1

CD 2012/4 Page 7 of 7

Section 15 - REGULATORY INFORMATION

ethanolamine (CAS: 141-43-5) is found on the following regulatory lists;

"Australia Exposure Standards", "Australia Hazardous Substances", "Australia High Volume Industrial Chemical List (HVICL)", "Australia Inventory of Chemical Substances (AICS)", "Australia National Pollutant Inventory", "Australia Standard for the Uniform Scheduling of Medicines and Poisons (SUSMP) - Appendix E (Part 2)", "Australia Standard for the Uniform Scheduling of Medicines and Poisons (SUSMP) - Appendix F (Part 3)", "Australia Standard for the Uniform Scheduling of Medicines and Poisons (SUSMP) - Schedule 4", "Australia Standard for the Uniform Scheduling of Medicines and Poisons (SUSMP) - Schedule 5", "Australia Standard for the Uniform Scheduling of Medicines and Poisons (SUSMP) - Schedule 6", "FisherTransport Information", "GESAMP/EHS Composite List - GESAMP Hazard Profiles", "IMO IBC Code Chapter 17: Summary of minimum requirements", "IMO MARPOL 73/78 (Annex II) - List of Noxious Liquid Substances Carried in Bulk", "International Council of Chemical Associations (ICCA) - High Production Volume List", "OECD List of High Production Volume (HPV) Chemicals", "OSPAR National List of Candidates for Substitution - Norway"

water (CAS: 7732-18-5) is found on the following regulatory lists;

"Australia High Volume Industrial Chemical List (HVICL)", "Australia Inventory of Chemical Substances (AICS)", "IMO IBC Code Chapter 18: List of products to which the Code does not apply", "International Fragrance Association (IFRA) Survey: Transparency List", "OECD List of High Production Volume (HPV) Chemicals", "OSPAR National List of Candidates for Substitution - Norway"

No data for Ultrasonic Cleaning Liquid #745-7494 (CW: 4764-48)

Section 16 - OTHER INFORMATION

■ Classification of the preparation and its individual components has drawn on official and authoritative sources as well as independent review by the Chemwatch Classification committee using available literature references.

A list of reference resources used to assist the committee may be found at:

www.chemwatch.net/references.

■ The (M)SDS is a Hazard Communication tool and should be used to assist in the Risk Assessment. Many factors determine whether the reported Hazards are Risks in the workplace or other settings.

This document is copyright. Apart from any fair dealing for the purposes of private study, research, review or criticism, as permitted under the Copyright Act, no part may be reproduced by any process without written permission from CHEMWATCH. TEL (+61 3) 9572 4700.

Issue Date: 10-Jan-2013

Print Date: 10-Jan-2013

This is the end of the MSDS.