

Wiha Standard bit.

Full programme range in outstanding quality.

Style C 6.3 (1/4").



7015 Z Standard bit, TORX®, style C 6.3.

Material: High grade chrome-vanadium steel, through hardened.
Drive: DIN 3126, ISO 1173, style C 6.3.
Application: For all types of screw applications in trade and industry.

Order-No.	Drive	Length	Width
26250 1	T3	25	10
25097 0	T4	25	10
01711 8	T5	25	10
01712 5	T6	25	10
01713 2	T7	25	10
01714 9	T8	25	10
01715 6	T9	25	10
01716 3	T10	25	10
01717 0	T15	25	10
01718 7	T20	25	10
01719 4	T25	25	10
01720 0	T27	25	10
01721 7	T30	25	10
01722 4	T40	25	10
01723 1	T45	35	10
01724 8	T50	35	10



7015K Z Standard bit, TORX® conic, style C 6.3.

Material: High grade chrome-vanadium steel, through hardened.
Drive: DIN 3126, ISO 1173, style C 6.3.
Application: For all types of screw applications in trade and industry.
Extra: Conical shape for a perfect clamping of the screw.

Order-No.	Drive	Length	Width
04925 6	T10	25	10
04926 3	T15	25	10
04927 0	T20	25	10
04928 7	T25	25	10
04929 4	T27	25	10
04930 0	T30	25	10
04931 7	T40	25	10



7015 Z TR Standard bit, TORX® H, style C 6.3.

Material: High grade chrome-vanadium steel, through hardened.
Drive: DIN 3126, ISO 1173, style C 6.3.
Application: For all types of screw applications in trade and industry.
Extra: Hole in the bit tip for TORX® Tamper Resistant security screws.

Order-No.	Drive	Length	Width
03115 2	T7H	25	10
03117 6	T8H	25	10
01726 2	T9H	25	10
01727 9	T10H	25	10
01728 6	T15H	25	10
01729 3	T20H	25	10
01730 9	T25H	25	10
01731 6	T27H	25	10
01732 3	T30H	25	10
01733 0	T40H	25	10

Style C 6.3 (1/4").



7016 Z Standard bit, TORX PLUS®, style C 6.3.

Material: High grade chrome-vanadium steel, through hardened.
Drive: DIN 3126, ISO 1173, style C 6.3.
Application: For all types of screw applications in trade and industry.
Extra: Reinforced profile cross-section transfers approx. 25% more torque than with a TORX® profile.

Order-No.	Drive	Length	Width	Notes
25994 5	3IP	25	10	NEW
25996 9	4IP	25	10	
25998 3	5IP	25	10	
23173 6	6IP	25	10	
23175 0	7IP	25	10	
23177 4	8IP	25	10	
23179 8	9IP	25	10	
23181 1	10IP	25	10	
23183 5	15IP	25	10	
23185 9	20IP	25	10	
23187 3	25IP	25	10	
23189 7	27IP	25	10	
23191 0	30IP	25	10	
23193 4	40IP	25	10	



7016 Z IPR Standard bit, TORX PLUS® Security, style C 6.3.

Material: High grade chrome-vanadium steel, through hardened.
Drive: DIN 3126, ISO 1173, style C 6.3.
Application: For all types of screw applications in trade and industry.
Attention: Security profile - sold only to authorised customers. Written proof of authorisation must be received.

Order-No.	Drive	Length	Width
26346 1	10IPR	25	10
26347 8	15IPR	25	10
26348 5	20IPR	25	10
26349 2	25IPR	25	10
26350 8	30IPR	25	10
26351 5	40IPR	35	10

Style C 6.3 (1/4").



7013 Z Standard bit, hex, style C 6.3.

Material: High grade chrome-vanadium steel, through hardened.
Drive: DIN 3126, ISO 1173, style C 6.3.
Application: For all types of screw applications in trade and industry.

Order-No.	Drive	Length	Width
04011 6	1.5	25	10
01703 3	2.0	25	10
01704 0	2.5	25	10
01705 7	3.0	25	10
01706 4	4.0	25	10
01707 1	5.0	25	10
01708 8	6.0	25	10
01709 5	8.0	25	10
01710 1	10.0	25	10



7013R Z Standard bit, hex, style C 6.3.

Material: High grade chrome-vanadium steel, through hardened.
Drive: DIN 3126, ISO 1173, style C 6.3.
Application: For all types of screw applications in trade and industry. Insert screws into or remove from boreholes, especially in difficult to access areas.
Extra: MagicRing® made from spring steel holds all standard screws in every position.

Order-No.	Drive	Length	Width
22955 9	3.0	25	10
22956 6	4.0	25	10
22957 3	5.0	25	10
22958 0	6.0	25	10



7013 Z TR Standard bit, hex Tamper Resistant, style C 6.3.

Material: High grade chrome-vanadium steel, through hardened.
Drive: DIN 3126, ISO 1173, style C 6.3.
Application: For all types of screw applications in trade and industry.
Extra: Hole in the tip of the bit for hex Tamper Resistant security screws.

Order-No.	Drive	Length	Width
25560 2	TR2.0	25	10
25561 9	TR2.5	25	10
25562 6	TR3.0	25	10
25563 3	TR4.0	25	10
25564 0	TR5.0	25	10

Style C 6.3 (1/4").



7017 Z Standard bit, ball end hex, style C 6.3.

Material: High grade chrome-vanadium steel, through hardened.
Drive: DIN 3126, ISO 1173, style C 6.3.
Application: For all types of screw applications in trade and industry. Especially for screws that are difficult to access.
Extra: The ball end enables the user to work at angles up to 25°.

Order-No.	Drive	Length	Width
01734 7	1.5	38	10
01735 4	2.0	38	10
01736 1	2.5	38	10
01737 8	3.0	38	10
01738 5	4.0	38	10
01739 2	5.0	38	10
01740 8	6.0	38	10



7017R Z Standard bit, ball end hex, style C 6.3.

Material: High grade chrome-vanadium steel, through hardened.
Drive: DIN 3126, ISO 1173, style C 6.3.
Application: For all types of screw applications in trade and industry. Insert screws into or remove from boreholes, especially in difficult to access areas.
Extra: MagicRing® made from spring steel holds all standard screws in every position. Ball end allows a working angle up to 25°.

Order-No.	Drive	Length	Width
22959 7	3.0	38	10
22960 3	4.0	38	10
22961 0	5.0	38	10
22962 7	6.0	38	10