

0 601 868 101 – GSR 12V-15

Material number	0 601 868 101	0 601 868 17A	0 601 868 178
EAN	3165140538473	3165140764940	3165140764926
1/2 L-BOXX inlay for tool 1 600 A00 2V8	✓		
2 x battery GBA 12V 2.0Ah 1 600 Z00 02X		✓	✓
Cardboard box	✓		
Charger GAL 12V-20 Professional		✓	
L-BOXX 102 1 600 A00 1RP			✓
Quick charger GAL 1230 CV 1 600 A01 16B			✓
Packaging dimensions (width x length x height)	220 x 360 x 95 mm		355 x 442 x 115 mm
Battery voltage	12.0 V	12.0 V	12.0 V
Weight incl. battery	1,0 kg		1,0 kg
Battery capacity			2,0 Ah
Charging time (80%/100%) approx.			35/45 min [2.0 Ah]

Technical data

Technical data

Torque (soft/hard/max.)	15/30/- Nm
No-load speed (1st gear / 2nd gear)	0 – 400 / 0 – 1,300 rpm
Chuck capacity, min./max.	1 / 10 mm
Battery voltage	12 V
Torque settings	20+1

Drilling diameter

Max. drilling diameter in wood	19 mm
Max. drilling diameter in steel	10 mm

Screw diameter

Max. screw diameter	7 mm
---------------------	------



Sales information

Positioning

- The handy powerhouse

User benefit

- At 169 mm it has an extremely short design for optimum handling, especially when performing drilling and screwdriving applications overhead and in tight spaces
- Professional performance: 2-speed gearbox ensures a powerful 15 Nm (soft screwdriving application) when drilling (up to 19 mm) and screwdriving (up to 7 mm)
- Professional quality 10 mm Auto-Lock drill chuck

