

# M6/8.STP



Products Low Voltage Products and Systems Connection Devices Terminal Blocks SNA Series

## General Information

<b>Extended Product Type:</b>	M6/8.STP
<b>Product ID:</b>	1SNA115277R2000
<b>EAN:</b>	3472591152777
<b>Catalog Description:</b>	M6/8.STP Screw Clamp Terminal Blocks - Disconnect with push-turn knob - with test socket - Grey, Yellow
<b>Long Description:</b>	- Ease your disconnect operations with the disconnect 1/4 turn push-turn knob, - Possibility to seal in the open position, - Ease your test operations with the built-in test socket.

## Additional Information

<b>ABB Industrial IT Suite:</b>	Control IT
<b>Ambient Air Temperature:</b>	Operation -55 ... +110 °C Storage -55 ... +110 °C
<b>Ambient Temperature:</b>	-5 ... +40 °C
<b>Color:</b>	Grey, Yellow
<b>Connecting Capacity Main Circuit UL/CSA:</b>	Screw Clamp / Rigid 1x 22 ... 8 AWG
<b>Connecting Capacity UL/CSA:</b>	Stranded 8 AWG
<b>Connecting Capacity Main Circuit:</b>	Screw Clamp / Flexible 1x 0.5 ... 6 mm <sup>2</sup> Screw Clamp / Rigid 1x 0.5 ... 10 mm <sup>2</sup>
<b>Connection Type:</b>	Screw clamp
<b>Country of Origin:</b>	France (FR)
<b>Customs Tariff Number:</b>	85369010
<b>Data Sheet, Technical Information:</b>	1SNC160019C0202
<b>Declaration of Conformity - CE:</b>	1SND225015U1000
<b>Degree of Protection:</b>	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP10
<b>EAC Certificate:</b>	1SND161009A1100
<b>EAN:</b>	3472591152777
<b>ETIM 4:</b>	EC000902 - (Knife) disconnect terminal block
<b>ETIM 5:</b>	EC000902 - (Knife) disconnect terminal block
<b>ETIM 6:</b>	EC000902 - (Knife) disconnect terminal block
<b>Environmental Information:</b>	1SND220002E1002
<b>Flammability According to UL94:</b>	V0
<b>Function:</b>	Disconnect
<b>IIT Publishing Status:</b>	Level 0 - Information enabled
<b>Industrial IT Certification Level:</b>	0
<b>Instructions and Manuals:</b>	1SNC160019C0202
<b>Insulation Material:</b>	Polyamide
<b>Invoice Description:</b>	M6/8.STP Screw Clamp Terminal Blocks - Disconnect with push-turn knob - with test socket - Grey, Yellow
<b>Maximum Operating Voltage UL/CSA:</b>	Main Circuit 600 V
<b>Minimum Order Quantity:</b>	25 piece
<b>Mounting Type:</b>	A: Closing operation (□) B: Opening operation (□) 1: Push (□) 2: Turn (□) 3: Stop
<b>Mounting on DIN Rail:</b>	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
<b>Number of Levels:</b>	1
<b>Object Classification Code:</b>	X
<b>Order Multiple:</b>	25 piece

Order multiple:	25 piece
Package Level 1 EAN:	3472591152777
Package Level 1 Gross Weight:	0.525 kg
Package Level 1 Height:	64 mm
Package Level 1 Length:	230 mm
Package Level 1 Units:	25 piece
Package Level 1 Width:	62 mm
Package Level 2 Gross Weight:	8.350 kg
Package Level 2 Height:	150 mm
Package Level 2 Length:	500 mm
Package Level 2 Units:	400 piece
Package Level 2 Width:	300 mm
Package Level 3 Units:	19200 piece
Pollution Degree:	3
Product Main Type:	M6/8.STP
Product Name:	Terminal block
Product Net Depth:	45 mm
Product Net Height:	55.5 mm
Product Net Weight:	21 g
Product Net Width:	8 mm
Product Packing Type:	Box
RMRS Certificate:	1SND161007A1101
Rated Cross-Section:	6 mm <sup>2</sup>
Rated Current (I <sub>n</sub> ):	Main Circuit 15 A
Rated Short-time Withstand Current (I <sub>cw</sub> ):	for 1 s 180 A
Rated Voltage (U <sub>r</sub> ):	500 V
Recommended Screw Driver:	4 mm
RoHS Date:	20050518
RoHS Information:	1SND230023F0208
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
Selling Unit of Measure:	piece
Short Description:	grey Screw Clamp Terminal Blocks M6/8.STP equipped with 2 test sockets DIA. 4 mm / .16"
Spacing:	8 mm
Sub-Function:	Disconnect with blade
Sub-Function 2:	With 2 test sockets DIA 4 mm 0.157 in
Sub-Function 3:	With push turn knob
Sub-Function 4:	With 2 test sockets DIA4
Tightening Torque:	acc. IEC 60947-1 0.8 N·m Manufacturer 1 N·m
Wire Stripping Length:	11.0 mm
cUL Certificate:	1SND161001A0209