







TPA IN FULL-LOCK (AS SHIPPED) POSITION
AND LATCH IN CLOSED POSITION




X-X



Y-Y






SEE NOTE 4



6	SLIDING LATCH	1	BLACK
5	FEMALE FRONT SEAL	1	RED
4	FEMALE BACK SEAL	1	BLACK
3	FEMALE REAR COVER	1	BLACK
2	FEMALE FRONT COVER	1	GREEN
1	FEMALE HOUSING	1	BLACK
No.	DESCRIPTION	QTY.	COLOUR
BILL OF MATERIAL			

TPA IN PRELOAD POSITION
AND LATCH IN OPEN POSITION



Z-Z

NOTES:

1. MATERIALS: HOUSINGS: POLYSTYRENE/NYLON BLEND, GLASS FILLED, UL 94 HB
SEALS: LIQUID SILICONE RUBBER
2. MX150 RECEPTACLE TERMINAL PER SD-33012-001 TO BE USED WITH THIS ASSEMBLY
CRIMPED WITH CABLE INSULATION OUTER DIAMETER IN THE RANGE 1.5mm TO 2.69mm
3. PRODUCT SPECIFICATION: PS-85070-001
4. PACKAGING SPECIFICATION: PK-85070-001, LATCH SHIPPED IN PARTIALLY OPEN POSITION
5. MATES WITH: SRC2 BLADE HOUSING ASSEMBLY PER SD-93288-001
6. APPLICATION SPECIFICATION: AS-85070-001
7. CONDUIT INTERFACE OPTIONS: REFER TO SD-93286-001

ADD NOTE 7 & CHG ISO
EC NO: WEU2012-0136
2012/02/07
DRWN:JSHEA
CHKD:JWALLACE
2012/02/10
APPR:EFOLAN
2012/02/22

QUALITY
SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES
(UNLESS SPECIFIED)

	mm	INCH
4 PLACES	±---	±---
3 PLACES	±---	±---
2 PLACES	±0.20	±---
1 PLACE	±0.5	±---
ANGULAR	±---	±---

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM ONLY

DRAWN BY	DATE	TITLE
JOCNNOR	2010/07/29	
CHECKED BY	DATE	
JWALLACE	2010/08/26	
APPROVED BY	DATE	
EFOLAN	2011/02/11	

MATERIAL NO.
932870001

SIZE
A2

SCALE
1:1

DESIGN UNITS
METRIC

DOCUMENT NO.

THIRD ANGLE
PROJECTION

SRC2 FEMALE 84 PIN
RECEPTACLE HOUSING
ASSEMBLY

molex

MOLEX INCORPORATED

SD-93287-001

SHEET NO.

1 OF 1