

## Touch panel - TP 3057M CO - 2700904

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Touch panel with 14.5 cm (5.7") graphics-capable TFT display, 256-step grayscale, 320 x 240 pixels, 1 x Ethernet, 1 x CANopen, 2 x USB, and integrated runtime of the Visu+ visualization software

### Why buy this product

- Easy installation, low installation depth, and compact design
- Short startup time
- Visu+ RT and AX OPC server integrated as standard in all devices
- Display available in sizes from 14.5 cm (5.7") to 30.7 cm (12")
- Available with PROFIBUS DP, MPI, CANopen, and serial interface as an option
- Can be extended with external CF card
- Energy efficient due to LED backlighting



### Key commercial data

Packing unit	1 pc
GTIN	 4 046356 585057
Custom tariff number	84714100
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

#### Dimensions

External dimension, width	203 mm
External dimension, height	147 mm
External dimension, depth	5 mm
Note regarding external dimension	Dimensions of the front plate
Installation dimension, width	195 mm

# Touch panel - TP 3057M CO - 2700904

## Technical data

### Dimensions

Installation dimension, height	139 mm
Installation dimension, depth	49 mm
Note regarding installation dimension	55 mm, approximately with fieldbus interface

### Display

Display	14.5 cm/5.7" TFT active
Resolution	320 x 240 Pixel (QVGA)
Backlighting	LED
Display backlight MTBF	40000 h
Touch screen	Resistive industrial touch screen
Colors	256-step grayscale

### Computer data

Processor	Xscale® PXA320, 806 MHz
RAM	128 MB SDRAM
Mass storage	1 GB Flash
Interfaces	2x USB Host 1.1, 1x Compact Flash®
Optional interfaces	1x CF card, type I and II
Network	1 x Ethernet (10/100 Mbps), RJ45
Operating systems	Windows CE 6.0
Power supply unit	24 V DC ±20%
Power consumption	9.6 VA

### General

Mounting type	Installation in front plate
Weight	1000 g

### Ambient conditions

Degree of protection	IP65 (front), IP20 (back)
Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Permissible humidity (operation)	20 % ... 85 % (non-condensing)
Permissible humidity (storage/transport)	20 % ... 85 % (non-condensing)
Vibration (operation)	DIN EN 60068-2-6
Shock	DIN EN 60068-2-27

### Classifications

#### eCl@ss

eCl@ss 4.0	27330202
eCl@ss 4.1	27330202
eCl@ss 5.0	27242215
eCl@ss 5.1	27242301

# Touch panel - TP 3057M CO - 2700904

## Classifications

### eCl@ss

eCl@ss 6.0	27242301
eCl@ss 7.0	27242301
eCl@ss 8.0	27242302

### ETIM

ETIM 2.0	EC001426
ETIM 3.0	EC001426
ETIM 4.0	EC001426
ETIM 5.0	EC001414

### UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43211903
UNSPSC 13.2	43201404

## Approvals

### Approvals

---

#### Approvals

UL Listed / cUL Listed / EAC / cULus Listed

---

#### Ex Approvals

---

#### Approvals submitted

---

### Approval details

UL Listed
-----------

cUL Listed
------------

EAC
-----

# Touch panel - TP 3057M CO - 2700904

## Approvals

cULus Listed

## Accessories

### Accessories

#### Battery module

Battery - HMI BATTERY - 2701383

CMOS battery



## Mounting material

Mounting kit - HMI WALL MOUNTING KIT - 2701380

HMI mounting kit for panel installation. The mounting kit includes 2 spring clips.



Mounting kit - HMI SCB MOUNTING KIT 4 - 2701384



HMI mounting kit for installation on a front plate. The mounting kit includes 4 x mounting brackets, 4 x screw threads, and a hexagonal wrench.

Mounting kit - HMI SCB MOUNTING KIT 6 - 2701385



HMI mounting kit for installation on a front plate. The mounting kit includes 6 x mounting brackets, 6 x screw threads, and a hexagonal wrench.

## Touch panel - TP 3057M CO - 2700904

### Accessories

Mounting kit - HMI SCB MOUNTING KIT 8 - 2701387



HMI mounting kit for installation on a front plate. The mounting kit includes 8 x mounting brackets, 8 x screw threads, and a hexagonal wrench.

---

### Operating stylus

Touch pen - TOUCH PEN - 2701379



Touch pen for HMIs, silver coated. Delivery includes self-adhesive pen holder.

---

### Parameterization memory

Memory - CF FLASH 256MB - 2988780



Program and configuration memory, plug-in, 256 MB

---

### Protective foil

Protective foil - 5,7" DISPLAY PROTECTIVE FOIL - 2701371



Protective film set comprising 10 pieces of film for a 5.7" display. Including a squeegee to apply film and instructions.

---

### Storage medium

USB memory stick - 2 GB USB STICK - 2701382



USB memory stick, 2 GB.

