

	1	2	3	4	5	6	7	8	9	10	11										
G	Drg No :- C 44600			INSTALLATION DRAWING																	
F	SPECIFICATION																				
	ACTUATING FORCE: -0.9N(3.2ozf)MAX																				
	RELEASE FORCE : -0.07N(0.25ozf)MIN																				
F	FREE POSITION :- 17.8 (0.70) MAX																				
	OPERATING POSITION :- 15.6 (0.61)																				
	MOVEMENT DIFFERENTIAL :- 0.4(0.016)MAX																				
E	OVERTRAVEL (AVAILABLE) :- DEPRESS TO CASE																				
D	SPECIAL FEATURE :- TESTED AND STAMPED TO UL AND CSA REQUIREMENTS																				
C	APPROVAL RATING :- 3 AMP - 125 OR 250V.AC.																				
B	DIAGRAM OF CONNECTIONS			<table><tr><td></td><td></td><td></td></tr><tr><td>1</td><td>FIRST ISSUE</td><td>15/08/02</td></tr><tr><td>ISSUE</td><td>REVISION</td><td>DATE</td></tr></table>												1	FIRST ISSUE	15/08/02	ISSUE	REVISION	DATE
1	FIRST ISSUE	15/08/02																			
ISSUE	REVISION	DATE																			
A																					

saia-burgess Smart solutions for comfort and safety Saia-Burgess Gateshead Limited Dukesway, Team Valley Trading Estate Gateshead, Tyne & Wear NE11 0UB Tel: +44 (0) 191 401 6100 Fax: +44 (0) 191 401 6322 www.saia-burgess.co.uk	THIRD ANGLE PROJECTION DO NOT SCALE ! THIS DRAWING MUST ONLY BE AMENDED ON A CAD SYSTEM ALL DIMENSIONS SPECIFIED IN MILLIMETRES	TOLERANCES UNLESS STATED:- NO DECIMAL PLACE ±0.50 1 DECIMAL PLACES ±0.25 2 DECIMAL PLACES ±0.15 ANGULAR ±1° INCH - OUNCE UNITS [IN BRACKETS]			APPROVED		TITLE / DESCRIPTION V4NSYR1 UL		
			DRAWN	T.BELL.	CHECKED BY				
			DATE	31/07/03	ENGINEERING		Drg No :- C 44600		A3
			SCALE	4/1	QUALITY ASSURANCE				