

STORAGE UNIT



OCXS Cabinet

6-drawer steel cabinet for storing large volume parts. Drawers dimensions: L 720 x W 540 mm.

A drawer locking system prevents opening more than one drawer at a time protecting the user from having the unit tip over.

Equipment:

- 1 drawer, height 75 mm, 60 kg load
- 4 drawers, height 150 mm, 120 kg load
- 1 drawer, height 275 mm, 120 kg load
- 1 safety lock with 2 keys for keeping all drawers locked shut.

Can be fitted with the following optional equipment:

- set of 8 plastic trays (ref. AMEB0006): set of 8 plastic ducts L 535 x W 90 x H 50 mm. Each duct features 4 removable and adjustable separators with 20 mm pitch.

Designed to fit drawer height 75 mm

- 4 metal ducts kit (ref. AMEA0050): set of 4 metal ducts L 535 x W 180 x H 124 mm. Each duct features 4 removable and adjustable separators with 20 mm pitch.

Width: 170 mm. Designed to fit drawer height 150 mm

- 4 metal ducts kit (ref. AMEA0051): set of 4 metal ducts 120 mm wide + 1 duct 240 mm wide, L 535 x H 124 mm. Each duct features 4 removable and adjustable separators with 20 mm pitch. Width: 170 and 230 mm, respectively. Designed to fit drawer height 150 mm

- hanging file folder kit (ref. ACCB0001): storage kit for drawer height 275 mm.

Dimensions (mm):	L 852 x D 625 x H 1030
------------------	------------------------