

Don't give up on that damaged thread!!! Studsaver will fix it - fast

Studsaver

- Suits threads M6 - 125, ¼" - 5"
- Restarts threads and helps restore threads and damaged bolts
- Easy to use and fits many different sizes

Double blade action

- Attach Studsaver above the damaged portion of the thread, close the jaws fingertight with the adjuster, and then turn.
- Studsaver has two specially hardened steel blades, which, guided by the good thread path, re-grooves over the damaged thread in minutes
- It doesn't matter if the metal is flattened, stripped or covered with paint, concrete, rust etc.
- The re-threading tool is also ideal for aluminium and plastic threads



Advantages

- No need to use force to re cut the thread
- No need to replace a hard to move bolt
- No need to keep an expensive set of thread-cutting tools
- Supplied with leverage handle for larger diameter threads

Universal Use

Suits virtually any thread forms both right and left hand in the ranges of M6 - 125, ¼" - 5" Comes with 60 degree cutting blades to suit metric, UNC and UNF thread types
Suitable for garage, construction, agriculture, maintenance workers - in fact any body who deals with threads.

Studsaver comes in three sizes:

- 90620 - ¼ to 7/8" & M6 to M20
- 92238 - to 1½" & M22 to M28
- 93200 - 1¼ to 5" & M32 to M1