

88

88 KNIPEX-"Alligator", Water Pump Pliers

DIN ISO 8976

88 01 180



88 01 250



88 02 250



88 06 250



88 07 250



- ▶ box-joint design:
high stability because of
double guide
- ▶ self-locking on pipes and nuts:
no slipping on the workpiece;
low handforce required
- ▶ guard prevents operators'
fingers being pinched
- ▶ favourable lever action:
optimum transmission of force
- ▶ gripping surfaces with special
hardened teeth, teeth hardness
approx. 61 HRC: low wear and
secure gripping
- ▶ Chrome Vanadium electric
steel, oil-hardened and
tempered



Self-locking on pipes and nuts. No slipping on the workpiece and less handforce required



Optimized shape of jaws for gripping pipes and nuts

Article-No.	EAN- Code	Head	Handles	Capacities		
				for pipes ○ 1/2 Inch	for nuts ⬡ mm (across flats)	g
	Length mm					
	4003773-					
88 00 250	019176	polished	red lacquered	1 1/2	36	300
88 01 180	034445	polished	with non-slip plastic coating	1 1/4	30	185
250	013341			1 1/2	36	315
300	013358			2	46	505
88 02 180	044222	polished	with two-colour	1 1/4	30	215
250	019282		dual component handles	1 1/2	36	355
300	029151			2	46	555
88 03 180	042860	chrome	with non-slip plastic coating	1 1/4	30	185
250	005742	plated		1 1/2	36	315
300	019312			2	46	505
88 05 180	060130	chrome	with two-colour	1 1/4	30	215
250	035497	plated	dual component handles	1 1/2	36	355
300	042389			2	46	555
88 06 250	039303	chrome	insulated with two-colours	1 1/2	36	370
		plated	dual component handles			
			⚡ 1000 V, VDE-tested			
88 07 250	019343	chrome	plastic dipped insulated	1 1/2	36	415
300	022350	plated	⚡ 1000 V, VDE-tested	2	46	635