


Actual information about approvals can be found on  
<http://www.schurter.com/approvals>



4721

4723

F

  
70° C

### Description

- Panel mount Screw-on version [4721]; Snap-in version [4723]; from front side
- Outlet shuttered, Protection class I [4721]; Pin temperature 70 °C [4723], Pin temperature 70 °C [4721]; Protection class I [4723]
- Solder terminals or quick connect terminals

### Other versions on request:

- for protection class II

### Technical data


Ratings IEC	10 A / 250 VAC; 50 Hz
Ratings UL/CSA	15 A / 250 VAC; 60 Hz
Dielectric strength	> 2 kVAC between L-N > 2 kVAC between L/N-PE (1 min/50 Hz)
Allowable operation temp.	-25 °C to 70 °C
Degree of protection	from front side IP30 acc. to IEC 60529
Protection class	Suitable for appliances with protection class I acc. to IEC 61140

Terminals	Solder terminals or quick connect terminals
Panel thickness s [4721]	Screw-on: max 8 mm Mounting screw torque max 0.5 Nm
Panel thickness s [4723]	Snap-in: 1/1.2/1.5/2/2.5/3 mm
Materials: Housing	Thermoplastic, black, UL 94V-0
Appliance-inlet /-outlet	F acc. to IEC/EN 60320-2-2, UL 498, CSA C22.2 no. 42 (for cold condition) pin-temperature 70 °C, 10 A, Protection class I

### Dimensions


4721

4723



E: Solder terminals 3.5 x 0.8 mm<TAB/><TAB/>28.4 mm  
 E: Quick connect terminals 4.8 x 0.8 mm<TAB/>>31.1 mm  
 E: Quick connect terminalse 6.3 x 0.8 mm<TAB/>>33.2 mm

E: Solder terminals 3.5 x 0.8 mm<TAB/><TAB/>28.4 mm  
 E: SQuick connect terminals 4.8 x 0.8 mm<TAB/>>31.1 mm  
 E: Quick connect terminals 6.3 x 0.8 mm<TAB/>>33.2 mm  
 S: 1.0/1.2/1.5/2.0/2.5/3.0 mm



Shutter operation:  
shutters opened by plug insertion

Shutter operation:  
shutters closed when plug is removed

### Variants

Order Number	Type	Panel mounting	Panel thickness s [mm]	Terminals
4721.0100	4721	Screw-on		Quick connect terminals 4.8 x 0.8 mm
4721.0000	4721	Screw-on		Quick connect terminals 6.3 x 0.8 mm
4721.0300	4721	Screw-on		Solder terminals 3.8 x 0.8 mm
4723.0100	4723	Snap-in	1	Quick connect terminals 4.8 x 0.8 mm
4728.0100	4723	Snap-in	1.2	Quick connect terminals 4.8 x 0.8 mm
4724.0100	4723	Snap-in	1.5	Quick connect terminals 4.8 x 0.8 mm
4725.0100	4723	Snap-in	2	Quick connect terminals 4.8 x 0.8 mm
4726.0100	4723	Snap-in	2.5	Quick connect terminals 4.8 x 0.8 mm
4727.0100	4723	Snap-in	3	Quick connect terminals 4.8 x 0.8 mm
4723.0000	4723	Snap-in	1	Quick connect terminals 6.3 x 0.8 mm
4728.0000	4723	Snap-in	1.2	Quick connect terminals 6.3 x 0.8 mm
4724.0000	4723	Snap-in	1.5	Quick connect terminals 6.3 x 0.8 mm
4725.0000	4723	Snap-in	2	Quick connect terminals 6.3 x 0.8 mm
4726.0000	4723	Snap-in	2.5	Quick connect terminals 6.3 x 0.8 mm
4727.0000	4723	Snap-in	3	Quick connect terminals 6.3 x 0.8 mm
4723.0300	4723	Snap-in	1	Solder terminals 3.8 x 0.8 mm
4728.0300	4723	Snap-in	1.2	Solder terminals 3.8 x 0.8 mm
4724.0300	4723	Snap-in	1.5	Solder terminals 3.8 x 0.8 mm
4725.0300	4723	Snap-in	2	Solder terminals 3.8 x 0.8 mm
4726.0300	4723	Snap-in	2.5	Solder terminals 3.8 x 0.8 mm
4727.0300	4723	Snap-in	3	Solder terminals 3.8 x 0.8 mm

Class II product also available on request  
Cord retaining clamps and insulation covers see accessories

### Packaging unit

100 Pcs

### Accessories

see page 277