


Diese Zeichnung/CAD-Daten dürfen ohne unsere Genehmigung weder vervielfältigt noch Dritten zugänglich gemacht werden. Ihre Benutzung ist nur für die Zwecke gestattet, für die wir sie ausdrücklich zur Verfügung gestellt haben. Die Zeichnung/CAD-Daten sind auf Verlangen jederzeit zurückzugeben. Zuwiderhandlungen sind strafbar und verpflichten zum Schadenersatz. Für den Fall der Anfertigung eines Patentes oder Gebrauchsmusters bleiben alle Rechte vorbehalten. ANSMANN betreibt eine Politik der kontinuierlichen Weiterentwicklung. Wir behalten uns daher das Recht vor, das auf diesem Datenblatt beschriebene Produkt jederzeit ohne Vorankündigung zu verändern oder zu verbessern. / This drawing/these CAD data must not be multiplied nor made accessible to third parties without our explicit approval. Their use is only permitted for those purposes for which we made them available expressly. On request this drawing/CAD data have to be returned to us at any time. Any contravention is punishable and leads to compensation. In case of application of a patent or a utility model all rights are reserved. ANSMANN pursues a policy of continuous development. Therefore we reserve the right to modify and improve at any time the product described in this data sheet without prior notice.



Technische Daten: Lampe/
technical data: lamp

Leuchtmittel/
illuminant

: LED

Zellenzahl/
number of cells

: 1x AA Mignon Alkaline, im Lieferumfang enthalten/
1x AA Mignon Alkaline, included

Schalterfunktion/
switch function

: AN-AUS/
ON-OFF

Leuchtweite (ANSI FL1)/
beam range (ANSI FL1)

: 30m

Sichtweite/
visual range

: 50m

Leuchtdauer/
operating time

: 6 Stunden/hours

Helligkeit/
brightness

: 30 Lumen
200 Lux

Schutzart/
protection

: IP54

Gehäuse/
housing

: Aluminiumgehäuse, matt schwarz lackiert
aluminium housing, matt black painted

Gewicht/
weight

: 66.5g mit Batterien/
66.5g with batteries

Approbationen/
approvals

: CE



Flagge am Tragegurt
flag at the carrying belt

Verwendungsbereich/Application range für Anfrage/for inquiry ANW201209				Zul. Abweichung/ Allowable deviation		Oberfläche/ Surface		Maßstab/Scale (DIN A4): 1:1		Gewicht/Weight	
								Werkstoff/Work material, Modell-Nr.			
				2012	Datum/Date	Name		Zeichnungsname/Drawing name			
				Erstellt/ Drawn by	30.03.	DC		Future1AA+ 2.Generation			
V3	date code changend and address added	20.01.14	CF					Zeichnungsnummer/Drawing number Artikelnummer/Part number 5816603 Blatt/ Sheet 1			
V2	technical data updated	28.08.13	CB								
V1	new torch design	31.10.12	DC								
V0	brightness added	22.02.10	TAR								
V0	data sheet created	13.11.08	RA								
Version	Änderung/Change	Datum/Date	Name	Ursprung/Origin Proj. 020/09/12		Ersatz für/Replaced by			Ersatz durch/Replacement through:		