


No. OF CCTS.	C	D	No. OF CCTS.	C	D
14	(51.51 ±.008) 2.028 ±.008	(55.37 ±.008) 2.180 ±.008	2	(3.96 ±.008) .156 ±.008	(7.82 ±.008) .308 ±.008
15	(55.47 ±.008) 2.184 ±.008	(59.33 ±.008) 2.336 ±.008	3	(7.92 ±.008) .312 ±.008	(11.79 ±.008) .464 ±.008
16	(59.44 ±.008) 2.340 ±.008	(63.30 ±.008) 2.492 ±.008	4	(11.89 ±.008) .468 ±.008	(15.75 ±.008) .620 ±.008
17	(63.40 ±.008) 2.496 ±.008	(67.26 ±.008) 2.648 ±.008	5	(15.85 ±.008) .624 ±.008	(19.71 ±.008) .776 ±.008
18	(67.36 ±.008) 2.652 ±.008	(71.22 ±.008) 2.804 ±.008	6	(19.81 ±.008) .780 ±.008	(23.67 ±.008) .932 ±.008
19	(71.32 ±.008) 2.808 ±.008	(75.18 ±.008) 2.960 ±.008	7	(23.77 ±.008) .936 ±.008	(27.64 ±.008) 1.088 ±.008
20	(75.29 ±.008) 2.964 ±.008	(79.15 ±.008) 3.116 ±.008	8	(27.74 ±.008) 1.092 ±.008	(31.60 ±.008) 1.244 ±.008
			9	(31.70 ±.008) 1.248 ±.008	(35.56 ±.008) 1.400 ±.008
			10	(35.66 ±.008) 1.404 ±.008	(39.52 ±.008) 1.556 ±.008
			11	(39.62 ±.008) 1.560 ±.008	(43.48 ±.008) 1.712 ±.008
			12	(43.59 ±.008) 1.716 ±.008	(47.45 ±.008) 1.868 ±.008
			13	(47.55 ±.008) 1.872 ±.008	(51.41 ±.008) 2.024 ±.008


NOTES:

- FOR USE WITH TERMINAL No. 2478 OR 2578
- ASSEMBLED CONNECTOR MATES WITH (1.14)/0.045 SQUARE OR ROUND PIN.
- EXTENDED PIN ENTRY WINDOWS ARE POSSIBLE.

RECOMMENDED P/C BOARD



OPTIONAL WINDOW DETAIL



DIRECTION OF
TERMINAL INSERTION.

ENG. No. DESIGNATION

3069 - G N 2

"G" GWT (750°C) PA66 BALCK

"2" INDICATES HOUSING WITHOUT RAMP
"BLANK" INDICATES HOUSING WITH RAMP

NO. OF CKT'S

WORKMANAGER ERROR EC NO: E2008-0403 DRAWN: BRUTTE 2008/01/30 CHKD: 2008/01/30 APPR: BMAGUIRE 2008/01/30	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 4:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
		mm	INCH	DRAWN BY BRIAN RUTLE 10/12/2007	DATE	TITLE HOUSING KK CONNECTOR (3.96)/0.156 CRIMP			
		4 PLACES ± --- ± ---	3 PLACES ± --- ± .010	CHECKED BY B. MAGUIRE 12/12/2007	DATE	750 GLOW WIRE VERSION			
		2 PLACES ± 0.25 ± .014	1 PLACE ± 0.35 ± ---	APPROVED BY B. MAGUIRE 14/12/2007	DATE	MOLEX INCORPORATED			
ANGULAR ± 2 °		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.		DOCUMENT NO.		SHEET NO. 1 OF 2	
SEE CHART		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

