

Plastic label - US-EMLP (27X12,5) - 0828798

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Plastic label, Card, white, Unlabeled, Can be labeled with: THERMOMARK CARD PLUS, THERMOMARK CARD, Mounting type: Adhesive, Lettering field: 27 x 12.5 mm




The figure shows the US-EMLP (20x9) version

Why buy this product

- The markers, which are supplied in uniform sheets, can be labeled quickly, easily, and cost-effectively using the THERMOMARK CARD
- The US-EMLP ... UniSheet labeling range includes self-adhesive device markers with good adhesive properties
- The perforated markers are easy to separate and can be easily fitted
- The sheets provide space for including function texts

Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 558921
Weight per Piece (excluding packing)	16.62 g
Custom tariff number	39199000
Country of origin	Germany

Technical data

Dimensions

Length (b)	27 mm
Height	0.5 mm
Width (a)	12.1 mm

Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Ambient temperature (assembly)	15 °C ... 25 °C

General

Color	white
Components	Silicone-free
Inflammability class according to UL 94	V0
Material	PVC

Plastic label - US-EMLP (27X12,5) - 0828798

Technical data

General

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	30
Number of individual labels per row	3
RoHS compliant	Yes
Adhesive	Acrylic
Printability	Thermal transfer
Device	5146464 THERMOMARK CARD
	5146451 THERMOMARK CARD-US-MAG1
Ink ribbon	0801371 THERMOMARK-RIBBON 110-TC
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN ISO 9227:2012-09
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	IEC 61010-1:2010-06
Result	Test passed
Burning behaviour	self-extinguishing
Foil strength	500 µm
Adhesive strength	50 µm

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

Plastic label - US-EMLP (27X12,5) - 0828798

Classifications

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Accessories

Accessories

Magazine

Magazine - THERMOMARK CARD-US-MAG1 - 5146451



Magazine for the THERMOMARK CARD printer, for accommodating US cards

Marker carriers

Marker carriers - CARRIER-EMP 22 (27X12,5) - 0827446



Marker carriers, black, Unlabeled, Mounting type: Screws, rivets, Diameter: 22 mm, Lettering field: 27 x 12.5 mm

Marker carriers - CARRIER-EMLP 22 (27X12,5) - 0828985



Marker carriers, black, Unlabeled, Mounting type: Screws, rivets, Diameter: 22 mm, Lettering field: 27 x 12.5 mm