

DX200 Premier

Features:

Pressure developing, two speed centrifugal extract fans suitable for wall, ceiling and window mounting (using glass mounting kit GMK). Stylish design and white appearance to complement and blend with modern decor.

Integral air operated back draught shutter.

Overrun timer version available.

Two minute delay start facility on DX200T and LVDX200T.

Clip off front cover for sleek clean appearance.

Totally enclosed, lubricated for life motors.

BEAB approved.

Safety Extra Low Voltage timer version available.

Side entry duct for flat ducting applications.

Easy cleaning and maintenance.

Conforms to Building Regulations Part F1.

3 Year guarantee (UK - ONLY)

Export Customers see your Local Distributor.



Benefits:

A choice of three duct positions.

Two speed extract fans.

Rating for single phase supplies 220 - 240V ~ 50Hz.

Air Flow at FID (m ³ /h):	106 (29.44 l/s)
Sound Pressure (dB(A)):	50
I.P. Rating:	X4
Bathroom Zones:	1,2&3
Fan Size (mm):	100 (3.94 inches)
RPM:	2400
Max Ambient Temperature:	40
Frequency (Hz):	50
Power (W):	35
Colour:	white
Voltage:	240V
Mounting:	Wall, Window, Ceiling Mounted, Ducted
Usage:	Utility, Bathroom, Shower Room, Toilet, Public Toilet, Washroom, Hotel