



Position switch, 1early N/O+1late N/C, wide, IP65_x, roller lever

Part no. AT0-11-2-IA/R
Article no. 083529
Catalog No. AT0-11-2-IA-R

General

| | | | |
|-----------------------|--|-----------------|--|
| Standards | | | IEC/EN 60947 |
| Climatic proofing | | | Damp heat, constant, to IEC 60068-2-78; damp heat, cyclical, to IEC 60068-2-30 |
| Ambient temperature | | °C | -25 - +70 |
| Mounting position | | | As required |
| Degree of Protection | | | IP65 |
| Terminal capacities | | mm ² | |
| Solid | | mm ² | 1 x (0.75 - 2.5) 2 x (0.75 - 1.5) |
| Flexible with ferrule | | mm ² | 1 x (0.5 - 1.5) 2 x (0.5 - 1.5) |

Contacts/switching capacity

| | | | |
|--|-----------|---------|----------|
| Rated impulse withstand voltage | U_{imp} | V AC | 6000 |
| Rated insulation voltage | U_i | V | 500 |
| Overvoltage category/pollution degree | | | III/3 |
| Rated operational current | I_e | A | |
| AC-15 | | | |
| 24 V | I_e | A | 10 |
| 220 V 230 V 240 V | I_e | A | 6 |
| 380 V 400 V 415 V | I_e | A | 4 |
| DC-13 | | | |
| 24 V | I_e | A | 10 |
| 110 V | I_e | A | 1 |
| 220 V | I_e | A | 0.5 |
| Supply frequency | | Hz | max. 400 |
| Short-circuit rating to IEC/EN 60947-5-1 | | | |
| max. fuse | | A gG/gL | 6 |
| Repetition accuracy | | mm | 0.02 |

Mechanical variables

| | | | |
|--|--------------|---------------|-------------|
| Lifespan, mechanical | Operations | $\times 10^6$ | 20 |
| Contact temperature of roller head | | °C | ≤ 100 |
| Mechanical shock resistance (half-sinusoidal shock, 20 ms) | | | |
| Standard-action contact | | g | 25 |
| Snap-action contact | | g | 2 |
| Operating frequency | Operations/h | | ≤ 6000 |

Actuation

| | | | |
|--|--|-----|--|
| Mechanical | | | |
| Actuating force at beginning/end of stroke | | N | 8.0/20.0 |
| Actuating torque of rotary drives | | Nm | 0.2 |
| Max. operating speed with DIN cam | | m/s | 1.5 |
| Notes | | | for angle of actuation $\alpha = 30^\circ$ |

Data for design verification according to IEC/EN 61439

| | | | |
|--|-------|---|----|
| Technical data for design verification | | | |
| Rated operational current AC-15 at 220 V, 230 V, 240 V | I_e | A | 6 |
| Rated operational current at 24 V | I_e | A | 10 |
| IEC/EN 61439 design verification | | | |

| | | |
|--|--|--|
| 10.2 Strength of materials and parts | | |
| 10.2.2 Corrosion resistance | | Meets the product standard's requirements. |
| 10.2.3.1 Verification of thermal stability of enclosures | | Meets the product standard's requirements. |
| 10.2.3.2 Verification of resistance of insulating materials to normal heat | | Meets the product standard's requirements. |
| 10.2.3.3 Verification of resistance of insulating materials to abnormal heat and fire due to internal electric effects | | Meets the product standard's requirements. |
| 10.2.4 Resistance to ultra-violet (UV) radiation | | Meets the product standard's requirements. |
| 10.2.5 Lifting | | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.2.6 Mechanical impact | | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.2.7 Inscriptions | | Meets the product standard's requirements. |
| 10.3 Degree of protection of ASSEMBLIES | | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.4 Clearances and creepage distances | | Meets the product standard's requirements. |
| 10.5 Protection against electric shock | | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.6 Incorporation of switching devices and components | | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.7 Internal electrical circuits and connections | | Is the panel builder's responsibility. |
| 10.8 Connections for external conductors | | Is the panel builder's responsibility. |
| 10.9 Insulation properties | | |
| 10.9.2 Power-frequency electric strength | | Is the panel builder's responsibility. |
| 10.9.3 Impulse withstand voltage | | Is the panel builder's responsibility. |
| 10.9.4 Testing of enclosures made of insulating material | | Is the panel builder's responsibility. |
| 10.10 Temperature rise | | The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices. |
| 10.11 Short-circuit rating | | Is the panel builder's responsibility. The specifications for the switchgear must be observed. |
| 10.12 Electromagnetic compatibility | | Is the panel builder's responsibility. The specifications for the switchgear must be observed. |
| 10.13 Mechanical function | | The device meets the requirements, provided the information in the instruction leaflet (IL) is observed. |

Technical data ETIM 5.0

| | | |
|---|----|--------------------|
| Sensors (EG000026) / End switch (EC000030) | | |
| Electric engineering, automation, process control engineering / Binary sensor technology, safety-related sensor technology / Position switch / Position switch (Type 1) (ecl@ss8-27-27-06-01 [AGZ382011]) | | |
| Width sensor | mm | 51 |
| Diameter sensor | mm | 0 |
| Height of sensor | mm | 51 |
| Length of sensor | mm | 0 |
| Rated operation current I _e at AC-15, 24 V | A | 10 |
| Rated operation current I _e at AC-15, 125 V | A | 0 |
| Rated operation current I _e at AC-15, 230 V | A | 6 |
| Rated operation current I _e at DC-13, 24 V | A | 10 |
| Rated operation current I _e at DC-13, 125 V | A | 1 |
| Rated operation current I _e at DC-13, 230 V | A | 0.5 |
| Switching function | | Slow-action switch |
| Output electronic | | No |
| Forced opening | | Yes |
| Number of safety auxiliary contacts | | 1 |
| Number of contacts as normally closed contact | | 1 |
| Number of contacts as normally open contact | | 1 |
| Number of contacts as change-over contact | | 0 |
| Type of interface | | None |
| Type of interface for safety communication | | None |
| Housing according to norm | | - |
| Construction type housing | | Cuboid |
| Material housing | | Plastic |
| Coating housing | | - |
| Type of control element | | Rotary lever |
| Alignment of the control element | | - |

| | | | |
|--------------------------------------|--|----|----------|
| Type of electric connection | | | - |
| With status indication | | | No |
| Suited for safety functions | | | Yes |
| Explosion safety category for gas | | | None |
| Explosion safety category for dust | | | None |
| Ambient temperature during operating | | °C | -25 - 70 |
| Degree of protection (IP) | | | IP65 |