

## Bus connector - IBS RL PLUG-LK/POF - 2731076

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Connector for the fiber optic bus with polymer fiber cable and for the power supply with QUICKON connection method




The illustration shows various product versions

### Why buy this product

- Fiber optic or twisted pair version
- QUICKON or spring-cage connection technology
- Polymer fibers do not need to be polished

### Key commercial data

Packing unit	1 pc
GTIN	 4 017918 185657
Weight per Piece (excluding packing)	106.5 g
Custom tariff number	85366990
Country of origin	Germany

### Technical data

Product type	Plug
Approval	UL Recognized
	cUL Recognized
	GOST
	cULus Recognized

### Classifications

#### eCl@ss

eCl@ss 4.0	27250281
eCl@ss 4.1	27250281
eCl@ss 5.0	27259205
eCl@ss 5.1	27242692
eCl@ss 6.0	27242692

# Bus connector - IBS RL PLUG-LK/POF - 2731076

## Classifications

### eCl@ss

eCl@ss 7.0	27242692
eCl@ss 8.0	27242692

### ETIM

ETIM 2.0	EC000313
ETIM 3.0	EC000313
ETIM 4.0	EC002584
ETIM 5.0	EC002584

### UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	39121311
UNSPSC 12.01	39121311
UNSPSC 13.2	39121311

## Approvals

### Approvals


#### Approvals

UL Recognized / cUL Recognized / GOST / cULus Recognized

#### Ex Approvals


#### Approvals submitted

## Approval details


UL Recognized 	
mm <sup>2</sup> /AWG/kcmil	22-18
Nominal current I <sub>N</sub>	4 A
Nominal voltage U <sub>N</sub>	250 V

## Bus connector - IBS RL PLUG-LK/POF - 2731076

### Approvals

cUL Recognized 	
mm <sup>2</sup> /AWG/kcmil	22-18
Nominal current I <sub>N</sub>	4 A
Nominal voltage U <sub>N</sub>	250 V

GOST 	
--	--

cULus Recognized 	
--	--