




DO NOT SCALE
DIMENSIONS IN mm

METRIC




THIRD ANGLE
PROJECTION




STRIP



LOOSE-PIECE



SECTION A-A




SECTION B-B

WIRE RANGE : 0,75-1,50 mm² (18-16 AWG)
INSUL. RANGE : 2,0 -2,5 mm (.080-.100)

NOTES :

- 1 FOR CRIMPDETAILS SEE AMP-SPEC. 114-19.000 .
- 2 MEETS PRODUCTSPECIFICATION 108-10042.
- 3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



CUSTOMER
DRAWING

FOR REFERENCE ONLY
WILL NOT BE UPDATED

DR. L.V.D.HEYDEN DATE 19.08.1987
CHK. P.V.D.HAGEN DATE
APP. L.V.SOEST DATE

PARTNUMBER	DIRECTION OF REEL	LOOSE-PIECE	MATERIAL	PLATING
163767-6	A		PH.BRONZE	SILVER
163767-5	A		PH.BRONZE	SEL.GOLD
163767-4	A		PH.BRONZE	EL.TIN
163767-3	B	164840-3	PH.BRONZE	SILVER
163767-2	B	164840-2	PH.BRONZE	SEL.GOLD
163767-1	B	164840-1	PH.BRONZE	EL.TIN

AMP

AMP-HOLLAND B.V.
's-Hertogenbosch, The Netherlands.

THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION AUG. ,1987

© COPYRIGHT 19 87 BY AMP-HOLLAND B.V.
ALL INTERNATIONAL RIGHTS RESERVED.
AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

WIRE RANGE	NAME	REV.DATE
-	SOCKET TYPE III CONTACT + SIZE 16	D M Y
INSUL.RANGE		20 09 88
SIZE A3	SHEET 1 OF 1	REV.LTR. f1
DWG. No. 163767		

NOTES	MATERIAL	THICKNESS	AREA
20	TIN	2,0 µm	ALL OVER
21	NICKEL GOLD	0,8 µm	ALL OVER CONTACT AREA BARREL
22	NICKEL GOLD	0,8 µm	ALL OVER CONTACT AREA
23	NICKEL GOLD	1,2 µm	ALL OVER CONTACT AREA
24	NICKEL SILVER	2,5 µm	ALL OVER CONTACT AREA BARREL
25	SILVER	0,5 µm	ALL OVER
26	SILVER	2,5 µm	ALL OVER

REV.s	ECN No.	DR.	DATE
F1	REVISED PER ECO-09-020689	KK	24AUG09

8 7 6 5 4 3 2 1