


# Header - PTSM 0,5/ 4-HH0-2,5-SMD R32 - 1808213

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Header, Nominal current: 6 A, Rated voltage (III/2): 160 V, Number of positions: 4, Pitch: 2.5 mm, Color: black, Contact surface: Tin, Mounting: SMD/THT/THR



## Key commercial data

Packing unit	600 pc
Minimum order quantity	600 pc
GTIN	 4 046356 697279
Weight per Piece (excluding packing)	1.47 g
Custom tariff number	85369010
Country of origin	Germany
Note	Made to Order (non-returnable)

## Technical data

### Dimensions

Length	7.5 mm
Height	5 mm
Pitch	2.5 mm
Dimension a	7.5 mm

### General

Range of articles	PTSM 0,5/..-HH-SMD
Insulating material group	IIIa
Rated surge voltage (III/3)	2.5 kV
Rated surge voltage (III/2)	2.5 kV
Rated surge voltage (II/2)	2.5 kV
Rated voltage (III/3)	50 V
Rated voltage (III/2)	160 V
Rated voltage (II/2)	160 V
Connection in acc. with standard	EN-VDE

# Header - PTSM 0,5/ 4-HH0-2,5-SMD R32 - 1808213

## Technical data

### General

Nominal current I <sub>N</sub>	6 A
Maximum load current	6 A
Insulating material	LCP
Inflammability class according to UL 94	V0
Color	black
Number of positions	4

## Classifications

### eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27141190
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402

### ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002637
ETIM 5.0	EC002637

### UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

## Approvals

### Approvals

---

#### Approvals

UL Recognized / UL Recognized / EAC

---

#### Ex Approvals

---

# Header - PTSM 0,5/ 4-HH0-2,5-SMD R32 - 1808213

## Approvals

Approvals submitted

### Approval details


UL Recognized	
	B
Nominal current $I_N$	5 A
Nominal voltage $U_N$	150 V

UL Recognized	
	B
Nominal current $I_N$	5 A
Nominal voltage $U_N$	150 V

EAC
-----

## Drawings

Drilling diagram



Dimensioned drawing

