

01

01 Combination Pliers, Chrome Vanadium

DIN ISO 5746



01 06 190

- ▶ for heaviest duty
- ▶ with gripping zones for flat and round material, suitable for versatile use
- ▶ with cutting edges for soft, hard and piano wire
- ▶ long cutting edges for thicker cables
- ▶ cutting edges additionally induction hardened, cutting edge hardness approx. 64 HRC
- ▶ particularly wear resistant gripping jaws due to additional hardening; hardness of the gripping jaws approx. 53 HRC
- ▶ Chrome Vanadium electric steel, oil-hardened and tempered

Article-No.	EAN-Code	Head	Handles	Cutting capacities				g
				⊘ mm	⊘ mm	⊘ mm	mm ²	
01 06 160	040729	chrome plated	insulated with two-colour dual component handles	2.0	1.5	10.0	16.0	210
190	040415	chrome plated	1000 V IEC / DIN EN 60 900 VDE-tested	2.5	2.0	13.0	25.0	300

08

08 Small Combination Pliers



08 05 110

- ▶ compact combination pliers for professionals and hobbyists
- ▶ with gripping zones for flat and round material, suitable for versatile use
- ▶ with cutting edges for soft and hard wire
- ▶ cutting edges additionally induction hardened, cutting edge hardness approx. 60 HRC
- ▶ Vanadium steel, oil-hardened and tempered

Article-No.	EAN-Code	Head	Handles	Cutting capacities				g
				⊘ mm	⊘ mm	⊘ mm	mm ²	
08 05 110	034957	chrome plated	with two-colour dual component handles	2.5	1.6	9.0	10.0	90