





LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			F1	REVISED PER ECO-11-004835	11MAR11	RK	HMR



RECOMMENDED PC BOARD LAYOUT (VIEWED FROM CONNECTOR SIDE)



SECTION U-U

TIPS	OBSOLETE	78.74 [3.100]	31	80.77 [3.180]	86.26 [3.396]	88.90 [3.500]	64	3-1761609-7	
		OBSOLETE	73.66 [2.900]	29	75.69 [2.980]	81.18 [3.196]	83.82 [3.300]	60	3-1761609-6
		OBSOLETE	60.96 [2.400]	24	62.99 [2.480]	68.48 [2.696]	71.12 [2.800]	50	3-1761609-5
		48.26 [1.900]	19	50.29 [1.980]	55.78 [2.196]	58.42 [2.300]	40	3-1761609-3	
		40.64 [1.600]	16	42.67 [1.680]	48.16 [1.896]	50.80 [2.000]	34	3-1761609-1	
		35.56 [1.400]	14	37.59 [1.480]	43.08 [1.696]	45.72 [1.800]	30	3-1761609-0	
		30.48 [1.200]	12	32.51 [1.280]	38.00 [1.496]	40.64 [1.600]	26	2-1761609-9	
		27.94 [1.100]	11	29.97 [1.180]	35.46 [1.396]	38.10 [1.500]	24	2-1761609-8	
		22.86 [.900]	9	24.89 [.980]	30.38 [1.196]	33.02 [1.300]	20	2-1761609-7	
		17.78 [.700]	7	19.81 [.780]	25.30 [.996]	27.94 [1.100]	16	2-1761609-6	
		15.24 [.600]	6	17.27 [.680]	22.76 [.896]	25.40 [1.000]	14	2-1761609-5	
		12.70 [.500]	5	14.73 [.580]	20.22 [.796]	22.86 [.900]	12	2-1761609-4	
	10.16 [.400]	4	12.19 [.480]	17.68 [.696]	20.32 [.800]	10	2-1761609-3		
	OBSOLETE	5.08 [.200]	2	7.11 [.280]	12.60 [.496]	15.24 [.600]	6	2-1761609-1	
	BLACK	73.66 [2.900]	29	75.69 [2.980]	81.18 [3.196]	83.82 [3.300]	60	1-1761609-6	
60.96 [2.400]		24	62.99 [2.480]	68.48 [2.696]	71.12 [2.800]	50	1-1761609-5		
48.26 [1.900]		19	50.29 [1.980]	55.78 [2.196]	58.42 [2.300]	40	1-1761609-3		
40.64 [1.600]		16	42.67 [1.680]	48.16 [1.896]	50.80 [2.000]	34	1-1761609-1		
30.48 [1.200]		12	32.51 [1.280]	38.00 [1.496]	40.64 [1.600]	26	1761609-9		
22.86 [.900]		9	24.89 [.980]	30.38 [1.196]	33.02 [1.300]	20	1761609-7		
17.78 [.700]		7	19.81 [.780]	25.30 [.996]	27.94 [1.100]	16	1761609-6		
15.24 [.600]		6	17.27 [.680]	22.76 [.896]	25.40 [1.000]	14	1761609-5		
10.16 [.400]		4	12.19 [.480]	17.68 [.696]	20.32 [.800]	10	1761609-3		
HOUSING COLOR	E	D	C	B	A	NO OF POS	PART NUMBER		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 30JUN05 B.CRISAMORE/DTI CHK 30JUN05 S.BOLASH APVD 30JUN05 M.WALMSLEY PRODUCT SPEC — APPLICATION SPEC —		NAME HEADER ASSEMBLY, SHORT EJECT LATCH, RIGHT ANGLE, LOW PROFILE, IDC —		SIZE A1		CAGE CODE 00779		DRAWING NO C-1761609		RESTRICTED TO —	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± 0.13[.005] 4 PLC ± — ANGLES ± —		MATERIAL FINISH		WEIGHT —		SCALE 4:1		SHEET 1 OF 1		REV F1	