



We Tame Photons to Work for You!



Products > LEDs > Thru-Hole > Rectangular > 2.5mm x 7mm



Features / Options

- ▶ State-of-the-Art, High Brightness Chip Technology
- ▶ Choice of Colors and Lens Finishes
- ▶ Lead Frame / Lens Casting Reliability
- ▶ Easy-to-Solder Leads, Tin Finish
- ▶ Available Bulk or on Tape and Reel
- ▶ Lead Trimming and Forming Available
- ▶ Custom Shapes, Easily Tooled, Low Minimum

Applications / Uses

- ▶ Board or Panel Indication or Illumination
- ▶ Annunciator and Control Panels
- ▶ Telecom Switches and Central Station Equipment
- ▶ Large Panel Indicators

Part Number:	Brightness	Dice Material	Emitted Color	Peak Wavelength	Epoxy Lens	Operating Typ Vf (V)	Intensity Typ, mcd @ 20 mA	View Angle 2x Theta		
SSL-LX25783GD	STANDARD	GaP	Green	565	Diffused	2.0	9	110		—
SSL-LX25783HGW	STANDARD	GaP	Red/Green	700	White Diffused	2	5	60		—
SSL-LX25783ID	STANDARD	GaAsP	Red	635	Diffused	2.0	9	80		—
SSL-LX25783SGD	STANDARD	GaP	Green	565	Diffused	2.2	35	110		—
SSL-LX25783SID	HIGH	AlInGaP	Red	636	Diffused	2.0	70	110		—
SSL-LX25783SOD	HIGH	AlInGaP	Orange	610	Diffused	2.0	70	110		—
SSL-LX25783SRD	STANDARD	GaAlAs	Red	660	Diffused	1.8	50	110		—
SSL-LX25783SUGD	HIGH	AlInGaP	Green	574	Diffused	2.2	20	110		—
SSL-LX25783SYD	HIGH	AlInGaP	Yellow	590	Diffused	2.0	160	110		—
SSL-LX25783USB	HIGH	InGaN	Blue	470	Diffused	3.5	50	110		—



SSL-LX25783YD		STANDARD	GaAsP	Yellow	585	Diffused	2.1	4	110	—
---------------	--	----------	-------	--------	-----	----------	-----	---	-----	---

UNCONTROLLED DOCUMENT

PART NUMBER
SSL-LX25783YD

REV.
A

REV.	E.C.N. NUMBER AND REVISION COMMENTS	DATE
A	E.C.N. #10702.	1.10.01



ELECTRO-OPTICAL CHARACTERISTICS $T_A=25^{\circ}\text{C}$ $I_f=20\text{mA}$

PARAMETER	MIN	TYP	MAX	UNITS	TEST COND
PEAK WAVELENGTH		585		nm	
FORWARD VOLTAGE		2.1	2.8	V_f	
REVERSE VOLTAGE	5.0			V_r	$I_f=100\mu\text{A}$
AXIAL INTENSITY		4		mcd	$I_f=20\text{mA}$
VIEWING ANGLE		110		$2x$ theta	
EMITTED COLOR:	YELLOW				
EPOXY LENS FINISH:	YELLOW DIFFUSED				

LIMITS OF SAFE OPERATION AT 25°C

PARAMETER	MAX	UNITS
PEAK FORWARD CURRENT*	155	mA
STEADY CURRENT	30	mA
POWER DISSIPATION	110	mW
DERATE FROM 25°C	-1.2	$\text{mW}/^{\circ}\text{C}$
OPERATING, STORAGE TEMP.	-55 TO +100	$^{\circ}\text{C}$
SOLDERING TEMP.	+260	$^{\circ}\text{C}$
1.6mm FROM BODY		5 SEC. MAX

* $t < 10\mu\text{s}$

*UNLESS OTHERWISE SPECIFIED TOLERANCES PER DECIMAL PRECISION ARE: X=±1 (±0.039), X.X=±0.5 (±0.020), X.XX=±0.25 (±0.010), X.XXX=±0.127 (±0.005). LEAD SIZE=±0.05 (±0.002), LEAD LENGTH=±0.75 (±0.030). MIN= +DECIMAL PRECISION -0.00 MAX.= +0.00 -DECIMAL PRECISION

UNCONTROLLED DOCUMENT

REV. A	PART NUMBER SSL-LX25783YD
-----------	------------------------------

CONFIDENTIAL INFORMATION
THE INFORMATION CONTAINED IN THIS DOCUMENT IS THE PROPERTY OF LUMEX INC. EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY LUMEX INC., THE HOLDER OF THIS DOCUMENT SHALL KEEP ALL INFORMATION CONTAINED HEREIN CONFIDENTIAL AND SHALL PROTECT SAME IN WHOLE OR IN PART FROM DISCLOSURE AND DISSEMINATION TO ALL THIRD PARTIES.



RELIABILITY NOTE
OUR MANY YEARS OF EXPERIENCE DATA ACCUMULATION INDICATE THAT SOLDER HEAT IS A MAJOR CAUSE OF EARLY AND FUTURE FAILURE. PLEASE PAY ATTENTION TO YOUR SOLDERING PROCESS.

DRAWN BY: CT	CHECKED BY:	APPROVED BY:	DATE: 8.4.92
			PAGE: 1 OF 1
			SCALE: N/A

2.3mm x 8mm RECTANGULAR LED,
585nm YELLOW, YELLOW DIFFUSED LENS.